


**Typ : SZ33045025054**

**RoHS Compliant**



$\varnothing D$  : 25 mm

L : 54 mm

mounting : M18 x 1,5

insulation : PVC  
 2500 Vac

Terminals : solder lugs

**Electrical Parameters**

Rated Capacitance ( $C_R$ ) @ 100 Hz / 20 °C	<b>33 + 33</b> $\mu$ F	
Tolerance	<b>-10/ +30</b> %	
Rated Voltage ( $U_R$ )	<b>450</b> V	
Surge Voltage ( $U_S$ ) max. 5 x 1 min / h	<b>495</b> V	
Reverse Voltage ( $U_U$ ) max. 1 s	<b>2</b> V	
Leakage Current ( $I_L$ ) @ $U_R$ / 5 min / 20 °C	<b>90</b> $\mu$ A	
ESR typ. @ 100 Hz / 20°C	<b>4823</b> m $\Omega$	
Tan $\delta$ typ. @ 100 Hz / 20°C	<b>10</b> %	
Z max. @ 10 kHz / 20°C	<b>3858</b> m $\Omega$	
ESL typ.	<b>30</b> nH	
Rated Ripple Current ( $I_R$ ) @ 100 Hz / 85 °C	<b>0,3</b> A	
Useful life @ $I_R, U_R, 85$ °C	<b>3000</b> h	
IEC Climatic category / Standards	<b>40/085/56</b>	<b>IEC 60384-4</b>
Applications		