

STANLEY PC510 / PC511 PLATFORM TRUCK



SXWTI-PC510



SXWTI-PC511

- **Industrial Aluminum Platform Truck**
Industrial Duty 4-wheeled Professional Platform Truck. Folds and opens in seconds. Easy to Use and Store.
- **Robust Design**
Made of lightweight and durable Aluminum. Tubing material of steel.
- **Steel Handle**
Strong and rigid metal handle for secure maneuvering of loads
- **Fit for use by almost anyone**
From industrial factories, commercial warehouses, retail stores, delivery services to professional movers

- | | | |
|-------------------------------|-----------------|-----------------------------------|
| | PC510 | PC511 |
| • Load Capacity: | 150 Kg | 250 Kg |
| • Open Dims: | 74 x 47 x 90 cm | 90 x 61 x 101 cm |
| • Folded Dims: | 74 x 47 x 25 cm | 90 x 61 x 33 cm |
| • Plastic Base Plate: | 74 x 48 cm | 90 x 61 cm |
| • Ball Bearing Wheels: | 10,1 x 3,9 cm | 17,2 x 5,2 cm Ball Bearing |
| • Net Weight: | 10,0 Kg | 17,1 Kg |

Item No.	Barcode	Capacity	G.W. (KGS)	N.W (KGS)	Packing	Packing detail	20ft Qty	40ft Qty
SXWTI-PC510	8717496635105	150kg	11,5	10	1	79*49*15cm	486	990
SXWTI-PC511	8717496635112	250kg	18,5	17,1	1	62.5*17*92.5cm	329	665