

ESG

ESG 9/17.7 K MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from the following manufacturers:

- Siemens
- Télémecanique
- ABB
- Beckhoff
- Lumberg
- Tags for all-purpose usage; self-adhesive or clip-on tags, depending on the type

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

Please note that these markers are not intended for printing with the SpeedMarking laser.

General ordering data

Type	ESG 9/17.7 K MC NE WS
Order No.	2047430000
Version	ESG, Device markers, 17.7 x 9 mm, Polyamide 66, Colour: White
GTIN (EAN)	4050118411140
Qty.	180 pc(s).
compatible printer	1324380000 1139400000 1925000000

Data sheet

ESG ESG 9/17.7 K MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	17.7 mm	Length (inches)	0.697 inch
Width	9 mm	Width (inches)	0.354 inch
Net weight	0.58 g		

General data

Application/manufacturer	LS switch, Self-adhesive	Colour	White
Length	17.7 mm	Material	Polyamide 66
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	V-2	Width	9 mm

Classifications

ETIM 6.0	EC001288	eClass 6.2	27-14-91-29
eClass 9.0	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Data sheet

ESG
ESG 9/17.7 K MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

Drawings

