



19" Double Section Wallmount Cabinet

6U, Flatpack, Gray, 600 mm (23.62") depth

Part No.: **713832**

EAN-13: 0766623713832 | UPC: 766623713832

The Intellinet Network Solutions wallmount cabinets offer you a flexible and comprehensive solution for your network installations. Our service starts with the shipping condition – get the completely assembled cabinet delivered or save space and money with the flatpack version.

In terms of housing, you can choose from among the extra-compact 10" cabinets and numerous 19" versions, with installation depths that range from 300 to 600 mm. With heights from 6 to 20 units in black (RAL9005) or gray (RAL7035), we offer you a solution for every need. The removable side panels, the lockable tempered glass-door that can be opened more than 180° and the optional double section make cabling and component exchange particularly easy.

Features:

- Flat Pack Design
- Ideal for 19" rackmount applications
- Maximum static load of 30 kg
- Usable depth: 385 mm (15.16 in.)
- Cable entry via rear or top panel
- 4MM toughened glass door
- Rear door for easy access to back of cabinet

- Reversible Front door
- Cold-rolled, galvanized SPCC steel with up to 1.5 mm thickness
- Ships Flatpacked
- Three-Year Warranty

Specifications:

General

- 19"
- Height: 6U
- Color: Gray RAL7035
- Complies with: ANSI/EIA RS-310-D; IEC60297-2; DIN41494, Part 1; DIN41494, Part 7

Dimensions

- 327 (h) x 540 (w) x 600 (d) mm
- 12.87 (h) x 21.26 (w) x 23.62 (d) in.
- Usable depth: 385 mm (15.16 in.)
- Maximum static load: 30 kg (66 lbs.)

Package Contents

- 2 Rail frames
- Top, Bottom, Front, Back & Side Panels
- Installation hardware



