




## 8-Port 10/100/1000 Mbps PoE Gigabit Desktop Switch



### Manual DN-95340

#### **Product Description:**

The DIGITUS Gigabit Desktop Switch with eight Power over Ethernet ports, offers your network significant improvement in terms of performance and efficiency. Thanks to PoE support, you only need a single (network) cable for power and data transfer. This switch makes it much easier to connect devices such as access points, network cameras, and IP telephones, and requires far less cabling than alternatives. It also allows you to extend your network in places where there are no power supply cables or sockets available. The switch does not require any configuration and therefore guarantees quick and seamless integration into the network. Moreover, the fanless design of the Switch ensures soundless operation, which makes this device the perfect solution for office environments and meeting rooms.



## Product Features:

- 8-Port 10/100/1000 Mbps PoE Gigabit Desktop Switch
- Ethernet IEEE802.3 / 802.3u / 802.3x/802.3ab / IEEE802.3 af/at
- Power over Ethernet (PoE) - You only need one cable for power and data transfer
- PoE power budget: 131 Watts (one to eight ports)
- Supports PoE: Provides 8 PoE Port, each port output 30W maximum power
- No configuration necessary
- Maximum power output: 135 Watts
- Status LEDs on each port
- Pin Feet: V+ (RJ45 Pin 1, 2) V- (RJ45 Pin 3, 6)
- Circuit isolation protection
- Backplane: 16Gbps
- MAC address table: 4K
- Dimensions (L x W x H): 250 mm x 115 mm x 39 mm
- Weight: 670g
- Color: Black

## Package Content:

- 8-Port Gigabit Switch
- Power Supply
- Manual
- Power cable

## Hardware Description:

### ■ The Front Panel


The front panel consists of LED Indications.

### ■ LED Indicators

Per Device: Power

Per Port: LINK/ACT (Link/Activity)

Per PoE Port: PoE



LED	Status	Color	Description
Power	On	Green	The switch is supplied with suitable power.
LINK/ACT	On	Green	The port is connecting.
	Blinks	-	The port is receiving or transmitting data.
	Off	-	The port is not linked successfully with the device.
PoE	On	Green	PD is connected
	Off	-	No PD is connected or power forwarding fails

### ■ The Rear Panel

The rear panel view of the PoE switch consists of a DC power connector.



### ■ RJ-45 Ports ( Auto MDI/MDIX )

8 auto-sensing ports of 10Base-T, 100Base-TX or 1000Base-TX connections.  
All ports can support Power over Ethernet to power devices.

Remark: MDI means connecting to another Hub or Switch while MDIX means connecting to a workstation or PC. Therefore, Auto MDI/MDIX means that you can connect to another Switch or workstation without changing pin-to-pin or crossover cabling.

### ■ DC Power Connector

Plug the female connector into the switch and male connector into a power outlet.  
Support input voltages 44~57 VDC.

## Product Specifications:

Item	Description
<b>Summarize</b>	
Fixed port	8x 10/100/1000Base-TX ports.
LED Indicators	PWR, PoE, Link/Act LED.
Input voltage	100V~240V AC, 50/60Hz (for power adapter) 48VDC (for switch)
Network Media	10BASE-TX: UTP category 5, 5e cable 100BASE-TX: UTP category 5, 5e cable 1000BASE-TX: UTP category 5, 5e cable
Forwarding Rate	10BASE-T: 14880pps / port 100BASE-TX: 148800pps / port 1000BASE-TX: 1488000pps / port
Power Supplies	135W
Operating temperature	0°C ~40°C .
Storage temperature	-10°C ~70°C .
Relative humidity	20%~85% (non-condensing).
Thermal methods	Fanless.
Switching capacity	16G.
MAC address table	4K.
Weight	<2 Kg

<b>PoE</b>	
PoE port	4/8 10/100/1000Base-TX ports. All 8 PoE ports or 4 PoE ports (Port 5-8)
PoE Standard	IEEE802.3af, IEEE802.3at, per port 15.4W, max 30W
Pin assignment	V+ (RJ45 Pin1, 2), V- (RJ45 Pin 3, 6).

Hereby ASSMANN Electronic GmbH, declares that this device is in compliance with the requirements of Directive 2014/30/EU (EMC), Directive 2014/35/EU (LVD) and the Directive 2011/65/EU for RoHS compliance. The complete declaration of conformity can be requested by post under the below mentioned manufacturer address.

**Warning:**

This device is a class B product. This equipment may cause some radio interference in living environment. In this case, the user can be requested to undertake appropriate measures to prevent interference.

**www.assmann.com**

Assmann Electronic GmbH  
Auf dem Schüffel 3  
58513 Lüdenscheid  
Germany

