



## SuperSpeed USB C HDMI Docking Converter

USB 3.1 C Male to HDMI, USB A and USB C Females, Multiport Converter, Black  
Part No.: **152037**

Easily connect a USB type-C device with an HDMI display and USB peripherals.

The Manhattan USB Type-C HDMI Docking Converter establishes a fast, simple and convenient link between newer USB type-C equipped media sources (computers, tablets, etc.) and existing HDMI displays (monitors, projectors, etc.), in either mirror- or extended-display mode. Create a mini-workstation by adding any USB 3.0 peripheral such as a mouse, keyboard, hub, external memory device and more with the integrated USB 3.0 port. Charge a device through the type-C charging port.

The Manhattan USB Type-C HDMI Docking Converter is easy and quick to install. No complicated configuration or setup is required to enhance the functionality of your type-C device. Its all-in-one design achieves a compact, integrated solution that eliminates unnecessary cables, tangles and clutter to keep installations and work spaces neat and orderly.

### Features:

- Multi-function docking converter connects a USB type-C port to an HDMI display, USB 3.0 port and type-C charging port
- Enjoy Ultra High-Definition(UHD) video and audio on an HDMI monitor, projector or other display device
- Mirror or Extended display modes support video resolutions up to 1080p@60Hz or 3840x2160p@30Hz, 4K, Full UHD
- Provides a standard USB 3.0 type-A port to connect mice, keyboards or portable memory devices (and more) or to charge and sync a portable electronic device
- USB-A port supports superspeed (5Gbps) data transmission, charging up to 7.5W (5V/1.5A); BC1.2 compliant
- USB-C port supports charging at 60W (20V@3A)
- USB-C supports 5Gbps data transmission
- Supports USB Power Delivery (PD) function up to 60 watts
- Compatible with all USB type-C supported desktops, notebooks and tablets including Apple MacBook, Chromebook Pixel and more
- Compliant with DisplayPort 1.2 Alternate Mode (DP Altmode)
- Plug and Play
- Fully shielded to reduce EMI and other interference sources
- Molded PVC boot and strain relief

For more information on Manhattan products, consult your local dealer or visit [www.manhattan-products.com](http://www.manhattan-products.com).

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- Lifetime Warranty

## Specifications:

### Standards and Certifications

- USB 3.1
- HDMI
- HDCP 1.4
- CE
- FCC
- RoHS2
- WEEE

### General

- Bus powered, up to 60 watts
- Overcurrent protection

### Connections

- USB type-C, 24-pin, male
- HDMI, 19-pin, female
- USB type-C, 24-pin, female
- USB type-A, 4-pin, female

### Video Resolutions

- 640 x 480, 800 x 600, 1024 x 768, 1920 x 1200, 3840 x 2160p@30Hz, 4K

### Physical

- 24-AWG cable gauge
- Mylar and aluminum shielding
- Withstanding voltage: 300 VDC
- Insulation resistance: 10 MOhm
- Conductive resistance: 5 Ohm
- Thermal plastic casing
- Length: 8 cm (3 in.)
- Weight: 31 g (1.1 oz.)
- Shielded
- Housing: ABS plastic

### Operating Environment

- Operation Temperature: 32 ~ 104°F (0 ~ 40°C)
- Storage Temperature: -4 ~ 140°F (-20 ~ 60°C)
- Humidity (noncondensing): 5 ~ 90%

### System Requirements

- Windows XP/Vista/7/8.1/10 or Linux or Mac 9.x/10.x or above

### Package Contents

- SuperSpeed USB C HDMI Docking Converter
- Quick Instruction Guide

