

1-800-383-7323 USA/CAN www.energizer.com


ENERGIZER CR2016

Lithium Coin



Industry Standard Dimensions

mm (inches)



Simulated Application test


Permissible deflection from a flat.

Typical Performance at 21°C (70°F)

Schedule:	Typical Drains:	Load	Cutoff
	at 2.9V		2.0V
	(mA)	(ohms)	(hours)
Continuous	0.097	30,000	928

Typical Discharge Characteristics

Load: 30K ohms - Continuous Typical Drain @ 2.9V: 0.097 mA



Specifications

Classification: "Lithium Coin"

Chemical System: Lithium / Manganese Dioxide (Li/MnO₂) **Designation:** ANSI / NEDA-5000LC, IEC-CR2016

Nominal Voltage: 3.0 Volts

Typical Capacity: 90 mAh (to 2.0 volts) (Rated at 30K ohms at 21°C)

Typical Weight: 1.9 grams (0.07 oz.)

Typical Volume: 0.5 cubic centimeters (0.03 cubic inch)

Max Rev Charge: 1 microampere

Energy Density: 122 milliwatt hr/g, 464 milliwatt hr/cc

Typical Li Content: 0.036 grams (0.0013 oz.)

UL Listed: MH12454

Shipping: For complete details, please reference: Global (except US): Special Provision A45 of the International


Air Transport Association Dangerous

Goods Regulations

United States: 49 CFR 173.185

Safety - lithium coin batteries lodged in the esophagus should be removed immediately. Leakage, chemical burns and potential perforation can occur within hours of ingestion. Seek medical attention immediately. Have physician call the NATIONAL BATTERY INGESTION HOTLINE for advice and follow-up (202)-625-3333) collect day or night.

Cross Section



Internal Resistance Characteristics


Pulse Test at 21°C (70°F)

Bkgnd Drain: Continuous

30K ohms 0.097 mA @2.9V

Pulse Drain: 2 seconds X 12 times/day

400 ohms 6.8 mA @2.7V



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.

© Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

Form No. EBC - 4118G Page 1 of 1