date/contact: 280416/CMA finishing: TKI last update: drawing: 94021 unit: -/ mm

1/4

tolerance:

page:

EVE GmbH Hollefeldstr. 16 48282 Emsdetten Tel.: +49 (0) 25 72 / 93 51 - 0 Fax: +49 (0) 25 72 / 93 51 - 24

www.eve.de • info@eve.de






1. Electrical Characteristics

Resonant Frequency (KHz)	4.5 ± 0.5	
Operating Voltage (Vp-p/max)	30	
Rated Voltage (Vp-p)	5.0	
Current Consumption (mA/max)	1.5 at Rated Voltage	
Sound Pressure Level (dB/min)	90 at 10cm at Rated Voltage	
Capacitance (pF)	20,000 ± 30% at 120 Hz	
Operating Temperature (°C)	- 20 ∼ +90	
Storage Temperature (°C)	-30 ~ +100	
Manual soldering conditions	350±20°C / within 5sec	

PS: Vp-p=1/2duty, square wave

2 . Typical Frequency Response Curve



PSOT3090L

date/contact: 280416/CMA finishing: TKI last update: drawing: 94021 unit: -/mm

2/4

tolerance:

page:

EVE GmbH Hollefeldstr. 16 48282 Emsdetten Tel.: +49 (0) 25 72 / 93 51 - 0 Fax: +49 (0) 25 72 / 93 51 - 24


www.eve.de • info@eve.de





3. Dimensions and Material

3-1 Shape



3-2 Material

Housing	ABS 777D UL94HB plastic resin (Color : Black)
Leading Wire	28AWG
Weight (Gram)	4.6

PSOT3090L

date/contact: 280416/CMA finishing: TKI last update: drawing: 94021 unit: -/ mm

3/4

Hollefeldstr. 16 48282 Emsdetten Tel.: +49 (0) 2572 / 93 51 - 0 Fax: +49 (0) 2572 / 93 51 - 24 www.eve.de • info@eve.de

EVE GmbH





4. TESTING METHOD

tolerance:


page:

· Standard Measurement conditions


Temperature:25±2 ℃ Humidity:45-60%

· Acoustic Characteristics

The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below.



In the measuring test, buzzer is placed as follows:



PSOT3090L

date/contact: 280416/CMA finishing: TKI last update: drawing: 94021

- / mm

4/4

Hollefeldstr. 16 48282 Emsdetten Tel.: +49 (0) 2572 / 93 51 - 0 Fax: +49 (0) 2572 / 93 51 - 24 www.eve.de • info@eve.de

EVE GmbH





5. RELIABILITY

unit:

page:

tolerance:

ITEMS	METHOD OF TEST AND MEASUREMENTS	PERFORMANCE
Coldness	After 98 hours of being exposed to -30 ${\mathcal C}$	No abnormality
withstanding	environment, should be returned to normal	shall exist
	environment for 2 hours, then re-proceed to test.	
Hotness	After 98 hours of being exposed to +100 $^\circ\!\!C$	No abnormality
withstanding	environment, should be returned to normal	shall exist
	environment for 2 hours, then re-proceed to test.	
Humidity	After 98 hours of being exposed to 40 $^\circ\!$	No abnormality
withstanding	environment in actual operation, should be	shall exist
	returned to normal environment for 2 hours, then	
	re-proceed to test.	
Durability	Testing after 1,000 hours actual continuous	No abnormality
	operation. (at standard measurement conditions)	shall exist
Drop	A natural drop from 75cm high down to the	No abnormality
withstanding	ground.	shall exist
Vibration	Vibration of 2,000 cycles per minute, 2mm	No abnormality
withstanding	amplitude, applied in X, Y and Z directions for 30	shall exist
	minutes each.	

6. PACKAGE METHOD

- <1 > 400pcs per box , Total 10 boxes per carton , total 4000pcs carton; Volume: L*W*H=510*330*300mm
- <2> RoHS Mark

