


## 1 . Electrical Characteristics

Resonant Frequency (KHz)	4.0 ± 0.5
Operating Voltage (Vp-p/max)	25
Rated Voltage (Vp-p)	5.0
Current Consumption (mA/max)	1.5 at Rated Voltage
Sound Pressure Level (dB/min)	80 at 10cm at Rated Voltage
Capacitance (pF)	13,000 ± 30% at 120 Hz
Operating Temperature (°C)	-20 ~ +100
Storage Temperature (°C)	-30 ~ +110
Wave soldering conditions (°C)	245±5°C for 3±0.5 seconds.
Manual soldering conditions (°C)	350±20°C / within 5sec


PS : Vp-p= 1/2duty , square wave

## 2 . Typical Frequency Response Curve



## 3 . Dimensions and Material

### 3-1 Shape



### 3-2 Material

Unit : mm

Housing	PBT1200 UL94HB plastic resin (Color : Black)
Leading Pin	Tin Plated Brass
Weight (Gram)	0.67


## 4. TESTING METHOD

### • *Standard Measurement conditions*


Temperature:  $25 \pm 2^\circ\text{C}$  Humidity: 45-60%

### • *Acoustic Characteristics*

The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below.



In the measuring test, buzzer is placed as follows:



## 5. RELIABILITY

ITEMS	METHOD OF TEST AND MEASUREMENTS	PERFORMANCE
Coldness withstanding	After 98 hours of being exposed to -30 °C environment, should be returned to normal environment for 2 hours, then re-proceed to test.	No abnormality shall exist
Hotness withstanding	After 98 hours of being exposed to +110 °C environment, should be returned to normal environment for 2 hours, then re-proceed to test.	No abnormality shall exist
Humidity withstanding	After 98 hours of being exposed to 40 °C 95%RH environment in actual operation, should be returned to normal environment for 2 hours, then re-proceed to test.	No abnormality shall exist
Durability	Testing after 1,000 hours actual continuous operation. (at standard measurement conditions)	No abnormality shall exist
Drop withstanding	A natural drop from 75cm high down to the ground.	No abnormality shall exist
Vibration withstanding	Vibration of 2,000 cycles per minute, 2mm amplitude, applied in X, Y and Z directions for 30 minutes each.	No abnormality shall exist

## 6. PACKAGE METHOD

<1> 1200pcs per box , Total 10 boxes per carton , total 12000pcs carton;  
 Volume: L\*W\*H=510\*330\*300mm

<2> RoHS Mark

