


1 . Electrical Characteristics

| | |
|----------------------------------|-----------------------------|
| Resonant Frequency (KHz) | 4.0 ± 0.5 |
| Operating Voltage (Vp-p/max) | 25 |
| Rated Voltage (Vp-p) | 5.0 |
| Current Consumption (mA/max) | 1.5 at Rated Voltage |
| Sound Pressure Level (dB/min) | 85 at 10cm at Rated Voltage |
| Capacitance (pF) | 14,000 ± 30% at 120Hz |
| Operating Temperature (°C) | -20 ~ +100 |
| Storage Temperature (°C) | -30 ~ +110 |
| Wave soldering conditions (°C) | 245±5°C for 3±0.5 seconds. |
| Manual soldering conditions (°C) | 350±20°C / within 5sec |


PS : Vp-p = 1/2duty , square wave

2 . Typical Frequency Response Curve



3 . Dimensions and Material

3-1 Shape



Unit : mm

3-2 Material

| | |
|---------------|--|
| Housing | PBT1200 UL94HB plastic resin (Color : Black) |
| Leading Pin | Tin Plated Brass |
| Weight (Gram) | 1.2 |


4. TESTING METHOD

• *Standard Measurement conditions*

Temperature: $25 \pm 2^\circ\text{C}$ Humidity: 45-60%

• *Acoustic Characteristics*

The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below.



In the measuring test, buzzer is placed as follows:



5. RELIABILITY

| ITEMS | METHOD OF TEST AND MEASUREMENTS | PERFORMANCE |
|------------------------|--|----------------------------|
| Coldness withstanding | After 98 hours of being exposed to -30 °C environment, should be returned to normal environment for 2 hours, then re-proceed to test. | No abnormality shall exist |
| Hotness withstanding | After 98 hours of being exposed to +110 °C environment, should be returned to normal environment for 2 hours, then re-proceed to test. | No abnormality shall exist |
| Humidity withstanding | After 98 hours of being exposed to 40 °C 95%RH environment in actual operation, should be returned to normal environment for 2 hours, then re-proceed to test. | No abnormality shall exist |
| Durability | Testing after 1,000 hours actual continuous operation. (at standard measurement conditions) | No abnormality shall exist |
| Drop withstanding | A natural drop from 75cm high down to the ground. | No abnormality shall exist |
| Vibration withstanding | Vibration of 2,000 cycles per minute, 2mm amplitude, applied in X, Y and Z directions for 30 minutes each. | No abnormality shall exist |

6. PACKAGE METHOD

- <1> 600pcs per box , Total 10 boxes per carton , total 6000pcs carton;
 Volume: L*W*H=510*330*300mm
- <2> 750pcs per box , Total 10 boxes per carton , total 7500pcs carton;
 Volume: L*W*H=510*330*300mm
- <3> RoHS Mark

