



NOTE:

1. Electrical test:
 - (1). 100% open short & miss wire test;
 - (2). Insulation resistance: DC 300V 10MΩ ;
 - (3). Contactor resistance: 3Ω Max;
 - (4). Dielectric strength: 100V AC/Minute, 1mA.
2. RoHS 2.0 AND REACH COMPLIANT
3. PRINTING: E258105 兄 AWM 80°C 30V VW-1 28AWG×1P 28AWG×2C
4. Operation temperature: -10°C ~ +60°C
 Storage temperature: -20°C ~ +75°C
 Operation humidity: 10%~85%
 Storage humidity: 10%~85%
 Voltage: 5V DC Current: 500mA
5. PACKING: 1PCS/Renkfroce giftbox

file No.	UNO Item No.	B/N	Length	Packing
29212c106	712172.01		150+20/-0mm	VP1:10.5x14cm (depth:2cm)
29212c106a	712172.33		300+20/-0mm	VP1:10.5x14cm (depth:2cm)

MATERIAL LIST:

④	OUTER MOLD	PVC COLOR FOR BLACK	2	
③	USB B TYPE	MINI 5PIN Type, The Pin Gold Plating, the shell for Nickel Plating	1	
②	USB A TYPE	USB A /M Type, The Pin Gold Plating, the shell for Nickel Plating	1	
①	CABLE	USB 2.0 (28AWGBC*1P)+(28AWGBC*2C)+AL/MG BRAID PVC JACKET COLOR: BLACK OD: 3.8±0.2mm	1	

NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK
		NEW	2016.06.21	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

CUSTOMER	ITEM NO.	SEE THE CHART
PRODUCT NAME	USB 2.0 AM/MINI 5P BM	UNO ITEM NO.
		UNIT MM
DRAWNBY	CHECKBY	APPOBY
ARVIN		DATE
		2016.06.21