


ENERGIZER XR91

ECO ADVANCED

AA



Industry Standard Dimensions




Specifications

Classification:	Alkaline
Chemical System:	Zinc-Manganese Dioxide (Zn/MnO ₂)
Environment:	No added mercury or cadmium
Designation:	ANSI-15A, IEC-LR6
Nominal Voltage:	1.5 volts
Nominal IR:	150 to 300 milliohms (fresh)
Operating Temp:	-18°C to 55°C (0°F to 130°F)
Typical Weight:	24.0 grams (0.8 oz.)
Typical Volume:	8.1 cubic centimeters (0.5 cubic inch)
Jacket:	Plastic Label
Shelf Life:	12 years at 21°C
Terminal:	Flat Contact
More Details:	On-Line Catalog-Application Manual


Milliamp-Hours Capacity

Continuous discharge to 0.8 volts at 21°C




Constant Power Performance

Typical Characteristics (21°C)



Constant Current Performance

Typical Characteristics (21°C)



Important Notice

This data sheet contains typical information specific to products manufactured at the time of its publication.

Physical values are for reference purposes and not intended for specific calculations.


©Energizer Brands, LLC - Contents herein do not constitute a warranty.




ENERGIZER XR91

Typical Discharge Profiles

100 mW Continuous Discharge (21°C)




250 mA Continuous Discharge (21°C)




Industry Standard Tests (21°C)



REMOTE/RADIO/CLOCK
52 mA 1 hr/8 hrs day



PORTABLE LIGHTING
3.3 ohm LIF



TOY
3.9 ohm 1 hr/day



Important Notice

This data sheet contains typical information specific to products manufactured at the time of its publication.

Physical values are for reference purposes and not intended for specific calculations.

©Energizer Brands, LLC - Contents herein do not constitute a warranty.