

Coaxial Cable Connector 16_N-50-3-27/133_N

Description

Right angle cable plug

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0314 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	

Related Documents

Outline drawing	DOU-00006427
Catalogue drawing	DOU-00006429
Assembly instruction	DOC-0000179148

Ordering Information

Bulk 100 pcs package	16_N-50-3-27/133_NH
Single package	16_N-50-3-27/133_NE

Additional Information

Suitable cables	RG_223_/U, ENVIROFLEX_142, RADOX_RF_400, RG_400_/U, RADOX_RF_142
-----------------	--