

## Coaxial Cable Connector 11\_N-50-7-43/133\_N

### Description

Straight cable plug

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	11 GHz

#### Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0303 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	

### Related Documents

Outline drawing	DOU-00006265
Catalogue drawing	DOU-00006132
Assembly instruction	DOC-0000179092

### Ordering Information

Bulk 100 pcs package	11_N-50-7-43/133_NH
Single package	11_N-50-7-43/133_NE

### Additional Information

Suitable cables	RG_213_U, GX_07272, G_07262, G_07272, RADOX_RF_213
-----------------	--