



WATERPROOF CONNECTORS



IP Rated Wire-to-Wire, Wire-to-Board

Connect with Us... Experience Makes the Difference





EDAC's waterproof Wire to Wire and Wire to Board series were designed for both extreme moisture and non-submersion applications supporting both low-level signal and power applications up to 12A and 300V.

Major applications include automotive, commercial and recreational vehicles, outdoor lighting, appliances, marine & aftermarket products, solar power installations, industrial equipment, process control, construction equipment, outdoor broadcast systems and portable devices.

EDAC's waterproof series come in pitch sizes ranging from 2.0mm to 5.9mm and feature silicone rubber gaskets either pre-installed in all-in-one plugs and receptacle housings or loose and available in a range of sizes to accommodate wire from 28AWG to 14AWG with either thin or standard wire insulation. Operating temperature range across the whole series of -40°C to +105°C.

Some of the unique features of EDAC's waterproof series include integral locking and double locking tabs designed to prevent accidental disengagements, keying system to prevent mismating, circuit sizes from 1 to 9 positions and visual confirmation of proper sealing.

Application tooling available includes hand tools for prototype and small builds to fully automated presses and applicators for high production applications. EDAC also offers the whole series in custom cables already fully assembled.

QUICK REFERENCE GUIDE

Series	Туре	Current Rating	Pitch	Pages
560	Wire to Wire	3A	2.5mm	2-3
560	Wire to Board	3A	2.5mm	2-3
566	Wire to Wire	2A	2.0mm	4-5
566	Wire to Board	2A	2.0mm	4-5
567	Wire to Wire	8A	5.9mm	6-7
568	Wire to Wire	12A	n.a.	8
572	Wire to Wire	10A	5.8mm	9-10
572	Wire to Wire	10A	5.8mm	9-10
Assembly Instructions	Assembly instructions for 560 and 572 Series		11-12	
Tools	Hand Crimp Tool, Ejection Tool and Auto-Crimp Machine			13

HOW TO USE THIS PRODUCT GUIDE

- Using the quick reference guide above, select the type of solution you need and proper current rating for your application and refer to the section of the product guide with the series you have selected.
- Select the part with the appropriate number of contacts required for your application and the mating connector if required. (Quantities shown are standard pack quantities)
- If applicable, using the Wire Seal Selection Guide in the series section, select the seal required for the wire gauge to be used in the application.
- Contacts are supplied on the reel & bulk. See specific series section for more information on the available standard quantities.

Custom assemblies are available in all series directly from EDAC, manufactured to your specifications. Contact EDAC or your local representative for more information.

WIRE GAUGE REFERENCE GUIDE

Gauge / AWG#	Sectional Area	Gauge / AWG#	Sectional Area
10	5.2mm ²	24	0.21mm ²
12	3.3mm ²	26	0.13mm ²
14	2.0mm ²	28	0.08mm ²
16	1.31mm ²	30	0.05mm ²
18	0.83mm ²	32	0.03mm ²
20	0.52mm ²	34	0.02mm ²
22	0.33mm ²	36	0.01mm ²







Wire to Wire / Wire to Board 2.5mm Pitch



- 2.5mm Pitch, Rated Current: 3A max
- Fully Waterproof with Double Latch Solution
- Available in Wire-to-Wire and Wire-to-Board Options
- Seals Preassembled into Housing; No External Sealing Required available in 2, 3, or 5 Positions
- True Crimp and Poke Solution
- Waterproofing Cap available to cover holes of wire seal
- Internal Polarization to Prevent Mismating
- · Available with wire already installed
- Waterproof Grade IP67 Certified



Specifications:

No. of Positions	2, 3, 5P
Pitch	2.5mm
Rated Voltage	250V
Rated Current	3A max
Withstanding Voltage	1000V AC (rms)
Contact Resistance	15 mΩ max
Insulation Resistance	1000 MΩ min./DC500V
Temperature Range	-40°C to +105°C
PCB Thickness	1.6mm

Materials:

Crimp &	Housing	PBT, UL 94V-0
Poke	Contact	Phosphor Bronze
PCB	Housing	PBT with Glass, UL 94V-0
Header	Contact	Brass
Contact Plating		Tin Plating
Wire & Housing Seals		Silicone Rubber
Waterproofing Cap		PBT, UL 94V-0

Waterproofing Cap:

Part No.	
565-200-100	



Crimp Contact:

N	Male Contact (Pin)			
Part No	Part No AWG# Ins. Dia. Pcs/Ree			
565-290-731	20-22	Max. Ø1.7	8,000	
565-290-711	22-28	Max. Ø1.6	8,000	

**Crimp Contacts are also available in strips of 60pcs. Contact EDAC for more information.

Fem	Female Contact (Socket)			
Part No	Part No AWG# Ins. Dia. Pcs/Re			
565-290-741	20-22	Max. Ø1.7	8,000	
565-290-721	22-28	Max. Ø1.6	10,000	

**Wire seals, housing seals and retainers are already pre-assembled in the connector.




9.80

Rear Gasket (Wire Seal):

Applicable Contact	Wire O.D.	Color
565-290-711	Ø1.00 to	Yellow
565-290-721	Ø1.30	rellow
565-290-731	Ø1.30 to	Orango
565-290-741	Ø1.70	Orange




560-002-000-110



STYLE:

- 101 WHITE MALE HOUSING (ONLY FOR BOARD MOUNT CONTACTS)
- 301 BLUE MALE HOUSING (ONLY FOR BOARD MOUNT CONTACTS)
- 110 WHITE MALE HOUSING FOR WIRE INSULATION Ø1.00 TO Ø1.30
- 310 BLUE MALE HOUSING FOR WIRE INSULATION Ø1.00 TO Ø1.30
- 111 WHITE MALE HOUSING FOR WIRE INSULATION Ø1.30 TO Ø1.70
- 311 BLUE MALE HOUSING FOR WIRE INSULATION Ø1.30 TO Ø1.70
- 210 WHITE FEMALE HOUSING FOR WIRE INSULATION Ø1.00 TO Ø1.30
- 410 BLUE FEMALE HOUSING FOR WIRE INSULATION Ø1.00 TO Ø1.30 211 WHITE FEMALE HOUSING FOR WIRE INSULATION Ø1.30 TO Ø1.70
- 411 BLUE FEMALE HOUSING FOR WIRE INSULATION Ø1.30 TO Ø1.70

Assembly Layout





G-SEAI Waterproof Connectors


Wire to Wire / Wire to Board 2.5mm Pitch

Male Housing:


560-002-000-XXX



560-003-000-XXX



560-005-000-XXX



Male Housing:

Ø Wire	Housing	XXX	
Insulation	Color	^^^	
Ø1.00 to	White	110	
Ø1.30	Blue	310	
Ø1.30 to	White	111	
Ø1.70	Blue	311	

Female Housing:


560-002-000-XXX



560-003-000-XXX



560-005-000-XXX




Female Housing:


	Ø Wire	Housing	XXX	
	Insulation	Color	\\\\\	
İ	Ø1.00 to	White	210	
	Ø1.30	Blue	410	
	Ø1.30 to	White	211	
	Ø1.70	Blue	411	

PCB Header


560-002-420-XXX



560-003-420-XXX




560-005-420-XXX



PCB Header:

Housing	XXX	
Color	^^^	
White	101	
Blue	301	



NOTE: Waterproofing Cap is installed at the wire seal end to cover the unused holes.



Crimp Contact:



Wire to Wire / Wire to Board 2.0mm Pitch



- · 2.0mm Pitch, Rated Current: 2A max
- Fully Waterproof Solution available in 2, 3, 4, or 6 Positions (2 and 3 Positions Only for Wire to Board)
- Available in Wire-to-Wire and Wire-to-Board Options
- Seals preassembled into housing; no external sealing required
- True Crimp and Poke Solution
- Waterproofing cap available to cover holes of wire seal
- Available with wire already installed
- Waterproof Grade IP67 Certified



Specifications:

No. of Positions	2, 3, 4, or 6P
Pitch	2.0mm
Rated Voltage	250V
Rated Current	2A max
Withstanding Voltage	1000V AC (rms)
Contact Resistance	10 mΩ max
Insulation Resistance	1000 MΩ min./DC500V
Temperature Range	-40°C to +105°C
PCB Thickness	1.6mm

Materials:

Crimp &	Housing	PBT, UL 94V-0		
Poke	Contact	Phosphor Bronze		
PCB	Housing	PBT with Glass, UL 94V-0		
Header	Contact	Brass		
Contact Plating		Tin Plating		
Wire & Housing Seals		Silicone Rubber		
Waterproofing Cap		PBT, UL 94V-0		

Waterproofing Cap:


Part No	
566-200-100	

N	Male Contact	(Pin)	
Part No	AWG#	Ins. Dia.	Pcs/Reel
566-290-711	22-28	Ø1.0~Ø1.5	12,000
	-		

**Crimp Contacts are also available in strips of 60pcs. Contact EDAC for more information.

Female Contact (Socket)					
Part No	Part No AWG# Ins. Dia. Pcs/Reel				
566-290-721	566-290-721 22-28 Ø1.0~Ø1.5 12,000				

**Wire seals and housing seals are already pre-assembled in the connector.



Rear Gasket (Wire Seal):

Applicable Contact	Wire O.D.	Color	
566-290-711	Ø1.00 to Ø1.25	Light Blue	
566-290-721	Ø1.25 to Ø1.50	Orange	



Ordering Code:

566-002-000-710

SERIES: 566, WIRE TO WIRE WIRE TO BOARD

NO. OF CONTACTS: 002 - 2 CONTACTS 003 - 3 CONTACTS 004 - 4 CONTACTS

006 - 6 CONTACTS

CONTACT CODE: -

000 - NO CONTACTS (ONLY FOR CRIMP CONTACTS) 421 - BOARD MOUNT CONTACTS (PCB) ONLY FOR 2 & 3 PIN SIZE

701 - BLACK MALE HOUSING (ONLY FOR BOARD MOUNT CONTACTS)


710 - BLACK MALE HOUSING FOR WIRE INSULATION Ø1.00 TO Ø1.25


711 - BLACK MALE HOUSING FOR WIRE INSULATION Ø1.25 TO Ø1.50

810 - BLACK FEMALE HOUSING FOR WIRE INSULATION Ø1.00 TO Ø1.25

811 - BLACK FEMALE HOUSING FOR WIRE INSULATION Ø1.25 TO Ø1.50

Assembly Layout








G-SEAI Waterproof Connectors

Wire to Wire / Wire to Board 2.0mm Pitch

Male Housing:

566-002-000-XXX



566-003-000-XXX



566-004-000-XXX



566-006-000-XXX




Male Housing:


Ø Wire Insulation	Housing Color	XXX
Ø1.00 to Ø1.25	Black	710
Ø1.25 to Ø1.50	Black	711

Female Housing:


566-002-000-XXX




566-003-000-XXX



566-004-000-XXX



566-006-000-XXX



Female Housing:


Ø Wire Insulation	Housing Color	XXX
Ø1.00 to Ø1.25	Black	810
Ø1.25 to Ø1.50	Black	811


PCB Header

566-002-421-701



566-003-421-701






www.edac.net





Wire to Wire / Splash Proof 5.0x5.9mm Pitch



- 5.0mm x 5.9mm Pitch, Rated Current: 8A max
- Splashproof Solution available in 1, 2, 3, 4, 6, or 9 positions
- Available in Wire-to-Wire Options
- True Crimp and Poke Solution with various sized wire seals available
- Available with wire already installed
- Splash Proof Grade IP52 (JIS C0920) Certified



Specifications:

No. of Positions	1, 2, 3, 4, 6, or 9P
Pitch	5.0mm x 5.9mm
Rated Voltage	300V
Rated Current	8A max
Withstanding Voltage	1700V AC (rms)
Contact Resistance	10 mΩ max
Insulation Resistance	1000 MΩ min./DC500V
Temperature Range	-40°C to +105°C


Materials:

Housing	PBT, UL 94V-0		
Contact	Ph. Brz. or Brass		
Contact Plating	Tin Plating		
Wire Seal	Silicone Rubber		

Crimp Contact:

Male Contact (Pin)				
Part No (Material) AWG# Ins. Dia. Pcs/Reel				
570-290-751 (Brass)	14	Max. Ø3.1	4,000	
570-291-731 (Ph. Brz.)	20-16	Max. Ø3.1	4,000	
570-290-731 (Brass)	20-16	Max. Ø3.1	4,000	
570-290-711 (Brass)	22-20	Max. Ø2.7	4,000	

Female Contact (Socket)				
Part No (Material) AWG# Ins. Dia. Pcs/Reel				
570-290-761 (Brass)	14	Max. Ø3.1	4,000	
570-291-741 (Ph. Brz.)	20-16	Max. Ø3.1	4,000	
570-290-741 (Brass)	20-16	Max. Ø3.1	4,000	
570-291-721 (Ph. Brz.)	22-20	Max. Ø2.7	4,000	
570-290-721 (Brass)	22-20	Max. Ø2.7	4,000	



^{**}Crimp Contacts are also available in strips of 40pcs. Contact EDAC for more information.

Wire Seal:

Part No.	Wire O.D.	Color	AWG#	Ø Dia.	Height
570-260-001	Ø1.7~Ø2.1	Black	22	Ø 5.0	6.0
570-260-002	Ø2.1~Ø2.7	Light Blue	22-20	Ø 5.0	6.0
570-260-003	Ø2.1~Ø2.7	Blue	22-20	Ø 5.0	6.7
570-260-004	Ø2.7~Ø3.1	Brown	20-14	Ø 4.9	5.0

570-260-002

570-260-001



Ordering Guide:

SERIES: -

567-002-000-100

567, WIRE TO WIRE NO. OF CONTACTS: 001 - 1 CONTACT

002 - 2 CONTACTS

003 - 3 CONTACTS

004 - 4 CONTACTS

006 - 6 CONTACTS

009 - 9 CONTACTS

CONTACT CODE:


000 - NO CONTACTS (ONLY FOR CRIMP CONTACTS)

STYLE:

310 - WHITE MALE HOUSING FOR CRIMP CONTACTS

410 - WHITE FEMALE HOUSING FOR CRIMP CONTACTS Page 6

Assembly Layout



www.edac.net







Wire to Wire / Splash Proof 5.0x5.9mm Pitch

Male Housing:


567-001-000-310




567-004-000-310




567-002-000-310




567-006-000-310



567-003-000-310



567-009-000-310




Female Housing:


567-001-000-410




567-004-000-410



567-002-000-410




567-006-000-410



567-003-000-410




567-009-000-410





Wire to Wire / Splash Proof



- Rated Current: 12A max
- Splashproof Solution for Single Position
- Available in Wire-to-Wire Option
- True Crimp and Poke Solution with various sized wire seals available
- Available with wire already installed
- Splash Proof Grade IP52 (JIS C0920) Certified



Specifications:


Rated Voltage	300V
Rated Current	12A max
Withstanding Voltage	1700V AC (rms)
Contact Resistance	10 mΩ max
Insulation Resistance	1000 MΩ min./DC500V
Temperature Range	-40°C to +105°C

Male Contact (Pin)					
Part No (Material) AWG# Ins. Dia. Pcs/Re					
570-290-751 (Brass)	14	Max. Ø3.1	4,000		
570-291-731 (Ph. Brz.)	20-16	Max. Ø3.1	4,000		
570-290-731 (Brass)	20-16	Max. Ø3.1	4,000		
570-290-711 (Brass)	22-20	Max. Ø2.7	4,000		

3	
1.5	

23

Female Contact (Socket)					
Part No (Material)	AWG# Ins. Dia. Pcs/Reel				
570-290-761 (Brass)	14	Max. Ø3.1	4,000		
570-291-741 (Ph. Brz.)	20-16	Max. Ø3.1	4,000		
570-290-741 (Brass)	20-16	Max. Ø3.1	4,000		
570-291-721 (Ph. Brz.)	22-20	Max. Ø2.7	4,000		
570-290-721 (Brass)	22-20	Max. Ø2.7	4,000		



570-260-004

Materials:

Housing	PBT, UL 94V-0
Contact	Ph. Brz. or Brass
Contact Plating	Tin Plating
Wire Seal	Silicone Rubber

^{**}Crimp Contacts are also available in strips of 40pcs. Contact EDAC for more information.

Wire Seal:

6.0
6.0
6.7
5.0

570-260-002


570-260-001



Ordering Guide:

Crimp Contact:


568-001-000-100



Male Housing:



568-001-000-200



Female Housing:



Wire to Wire / Wire to Board 5.8mm Pitch



- 5.8mm Pitch, Rated Current: 10A max
- Fully Waterproof with Double Latch Solution
- Available in Wire-to-Wire and Wire-to-Board Options
- · Seals preassembled into housing; no external sealing required available in 1, 2, or 3 Positions
- True Crimp and Poke Solution
- Internal Polarization to Prevent Mismating
- Available with wire already installed
- · Wide range of wire sizes available
- Waterproof Grade IP67 Certified



Specifications:

No. of Positions	1, 2, 3P
Pitch	5.8mm
Rated Voltage	300V
Rated Current	10A max
Withstanding Voltage	1700V AC (rms)
Contact Resistance	10 mΩ max
Insulation Resistance	1000 MΩ min./DC500V
Temperature Range	-40°C to +105°C
PCB Thickness	1.6mm

Materials:

Crimp &	Housing	PBT, UL 94V-0
Poke	Contact	Ph. Brz. or Brass
	Housing	PBT with Glass, UL 94V-0
PCB Header	Contact	Brass
Contact Plating		Tin Plating
Wire & Housing Seals		Silicone Rubber

Crimp Contact:

Male Contact (Pin)				
AWG#	Ins. Dia.	Pcs/Reel		
14	Max. Ø3.1	4,000		
20-16	Max. Ø3.1	4,000		
20-16	Max. Ø3.1	4,000		
22-20	Max. Ø2.7	4,000		
	AWG# 14 20-16 20-16	AWG# Ins. Dia. 14 Max. Ø3.1 20-16 Max. Ø3.1 20-16 Max. Ø3.1		

Femal	e Contact (S	Socket)			
Part No (Material)	Part No (Material) AWG# Ins. Dia. Pcs				
570-290-761 (Brass)	14	Max. Ø3.1	4,000		
570-291-741 (Ph. Brz.)	20-16	Max. Ø3.1	4,000		
570-290-741 (Brass)	20-16	Max. Ø3.1	4,000		
570-291-721 (Pn. Brz.)	22-20	Max. Ø2.7	4,000		
570-290-721 (Brass)	22-20	Max. Ø2.7	4,000		



	_	16.60	_
2.50			
7			

^{**}Crimp Contacts are also available in strips of 40pcs. Contact EDAC for more information.

Wire Seal:

WILL OCUL					
Part No.	Wire O.D.	Color	AWG#	Ø Dia.	Height
570-260-001	Ø1.7~Ø2.1	Black	22	Ø 5.0	6.0
570-260-002	Ø2.1~Ø2.7	Light Blue	22-20	Ø 5.0	6.0
570-260-003	Ø2.1~Ø2.7	Blue	22-20	Ø 5.0	6.7
570-260-004	Ø2.7~Ø3.1	Brown	20-14	Ø 4.9	5.0

570-260-002

570-260-001





570-260-003 **Assembly Layout**

Ordering Guide:

572-002-000-100

572, WIRE TO WIRE WIRE TO BOARD

SERIES: -

NO. OF CONTACTS: 001 - 1 CONTACT 002 - 2 CONTACTS 003 - 3 CONTACTS

CONTACT CODE: -

000 - NO CONTACTS (ONLY FOR CRIMP CONTACTS)

420 - BOARD MOUNT CONTACTS


101 - WHITE MALE HOUSING (ONLY FOR BOARD MOUNT CONTACTS)

301 - BLUE MALE HOUSING (ONLY FOR BOARD MOUNT CONTACTS)

100 - WHITE MALE HOUSING FOR CRIMP CONTACTS

300 - BLUE MALE HOUSING FOR CRIMP CONTACTS

200 - WHITE FEMALE HOUSING FOR CRIMP CONTACTS 400 - BLUE FEMALE HOUSING FOR CRIMP CONTACTS



www.edac.net

^{**}Housing seals are already pre-assembled in the connector.





Wire to Wire / Wire to Board 5.8mm Pitch

Male Housing:

572-001-000-XXX



572-002-000-XXX



572-003-000-XXX




Male Housing:

Housing	XXX
Color	
White	100
Blue	300

Female Housing:


572-001-000-YYY



572-002-000-YYY



572-003-000-YYY




Female Housing:


YYY
111
200
400

PCB Header

572-001-420-XXX



572-002-420-XXX



572-003-420-XXX




PCB Header

Housing	XXX
Color	
White	101
Blue	301



ASSEMBLY INSTRUCTIONS 560 Series






STEP 2:


- Ensure that the back side of the contact is aligned to the open slot of the preassembled housing before inserting
- Insert the contact + wire assembly into the housing until a "click" sound is heard.
- · Illustrations are shown on:

Fig.4: Male Housing



STEP 1:

- Prepare the cable wire of stripped length of 2.0mm
- Crimp the contact to the cable wire as shown in Fig.1 for the female contact and in Fig.2 for the male contact



STEP 3:

- After the wires are inserted, press the rear insulator to finish the connector assembly
 NOTE: The 2 ribs of the rear insulator should be within the window opening of the housing
- · Illustrations are shown on:

Fig.5: Female Connector Assembly Fig.6: Male Connector Assembly








ASSEMBLY INSTRUCTIONS 572 Series





STEP 1:

- Prepare the cable wire of stripped length of 4.0mm
- Ensure that the wire seal's shoulder is properly placed on the contact, as shown in Fig.7
- · This is applicable to both Female and Male contacts

STEP 2:

• Crimp the contacts to cable + wire seal as shown on:

Fig.8: Male Contact Assembly Fig.9: Female Contact Assembly


STEP 3:


• In a position as shown in:

Fig.10: Male contact assembly's crimp side is aligned opposite the wider side of the male housing

Fig.11: Female contact assembly's crimp side is aligned opposite the lower latch of the female housing

 Insert the contact + wire assembly into the housing until a "click" sound is heard





www.edac.net

STEP 4:

 Press in the wire seal to finish the assembly, as shown in:

Fig.12: Male Connector Assembly

Fig.13: Female Connector Assembly



TOULS Hand Crimp Tool, Ejection Tool, Auto-Crimp Tool







AUTOMATIC CONTACT CRIMP MACHINE TOOL

- Part Number 516-280-700 for base machine
- Applicators available to crimp all 560, 566, 567, 568 and 572 series contacts
- All required guards for operator safety
- Easy access for all setting changes
- Foot switch to initiate crimp cycle
- Mounts to any bench surface
- Quick change applicators allow for fast conversions from one contact type to another
- Requires 110V 50/60Hz electrical supply

CONTACT HAND CRIMP TOOL

- Part Number: 565-280-210
- Hand crimp tool for 560, 567, 568 and 572 series contacts
- Manual hand crimp tool
- Uses contacts on carrier strip, crimps them and cuts the contacts from the carrier
- For 566 series, use crimper 566-280-200



CONTACT EJECTION TOOL

- Part Number: 570-280-300
- Ejection tool for 567, 568 and 572 series contacts



- Part Number: 565-280-301
- Ejection tool for 560 series contacts



