

# KERN ABT 120-5DNM

Das Premium-Modell mit Single-Cell Wägesystem



## Functions

Counting function:	yes
Function to save totals:	yes
Percentage determination:	yes
Standby function:	yes
Suspended weighing:	Hook
Vibration-free weighing (Animal weighing program):	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	10 °C

## Power supply

Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

## Service

DAkkS Certificate:	963-101
Verification:	965-201

## Category

Brand:	KERN
Category:	Balances
Product Group:	Analytical balance

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	430 x 685 x 650 mm
Gross weight:	12,600 kg
Net weight:	7,500 kg
Shipping method:	Parcel service

## Construction

Casing material:	metal
Dimensions draft shield (WxDxH):	200 x 240 x 260 mm
Dimensions housing (WxDxH):	215 x 340 x 335 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing space (WxDxH):	168 x 172 x 223 mm
Weighing surface (d):	80

## Measuring system

Adjustment options:	External calibration Internal calibration (auto) Internal calibration (manual)
Linearity:	0,050 mg   0,200 mg
n/a:	40 mg
Readout [d]:	0,010 mg   0,100 mg
Reproducibility:	0,020 mg   0,100 mg
Resolution:	4.200.000 1.200.000
Stabilisation time:	4 s   10 s
Warm up time:	8 h   8 h
Weighing range [Max]:	42 g   120 g
Weighing units:	ct g mg

## Display

Display digit height:	1,400 cm
-----------------------	----------

## Technical data about verification

Minimum load [Min]:	1 mg
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	I
Verification value [e]:	1 mg

## Counting

Counting resolution:	120000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg
Reference weight:	yes