






Dept Qty
DC 1
ED 1
IE 1
ISO 1
PD 1
R&D 1
SD 1
QA 1
QC 1
QE 1

The information provided herein is from CONNLY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNLY or its affiliates. Unauthorized use or reproduction of this information in any form or by any means, electronic or mechanical, including photocopying, recording, or by any information storage and retrieval system, without the prior written permission of CONNLY is strictly prohibited. CONNLY may enforce its intellectual property rights at its own discretion, failures or delays to exercise such rights does not constitute a waiver of such rights.




Dimension


Position	A±0.1	B±0.2	C±0.2	D±0.2		E±0.2
				Male	Female	
9P	10.16	30.80	24.99	17.90	16.33	19.00
15P	17.78	39.14	33.32	26.50	24.66	27.34
25P	30.48	53.04	47.04	40.00	38.38	41.24
37P	45.72	69.32	63.50	56.50	54.84	57.52



W/O Screw type



CC type



CS type




(Series Image-Reference Only)

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	YCH 02/01/07'		LJC 02/01/07'
E	DRAWING UPDATE	JLZ 09/14/20'		

- NOTES:
- Electrical characteristics:
 - 1.1 Contact resistance: 30mΩ Max. Initial.
 - 1.2 Dielectric withstanding voltage: 500V AC(rms) for 1 minute.
 - 1.3 Insulation resistance: 1000MΩ Min.
 - Environment characteristics:
 - 2.1.Temperature range: -40°C~+105°C.
 - Materials:
 - 3.1 Insulator:PBT+Glass fiber
 - 3.2 Shell:Steel
 - 3.3 Contact:Copper alloy
 - Product number code:

DS1036 - X X X X X X X - YT

- Screw type
 - X:W/O Screw
 - 1:CC type
 - 2:CS type
- Rivet type
 - P:W/ Thread(UNC #4-40)
 - N:W/O Thread(For W/O screw only)
- Contact plating
 - 2: Gold+Nickel
- Housing color
 - B: Black
 - U: Blue
- Strain relief
 - P:W/
 - N:W/O
- Connector type
 - M: Male F: Female
- No.of contacts
 - 09,15,25,37



GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	
X.	±0.60	X.	±5°	UNITS	mm	IDC D-SUB	
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1036 SERIES
.XX	±0.25	.XX	±2°	 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD			
DRAWING TYPE		CUSTOMER					
SCALE	1:1	SHEET	1 OF 1				
DRAWING NO.	C-DS1036-XXXXXXX-YT-E						