

VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

"Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success."

VC-450 E DIGITAL MULTIMETER

CE

VERSION 12/21

Nº 1500207

The VC-450 E professional digital multimeter is extremely impact resistant, dust tight and water-jet proof and therefore ideal for more demanding measurement tasks. This robust device can even withstand falls from heights of 2 metres. True RMS and a 6,000-count display provide accurate readings. Special built-in low impedance mode to eliminate stray or ghost voltages.

FEATURES:

CAT III 1000 V/CAT IV 600 V // True RMS // 3-Phase rotating direction display // Heavy-Duty Device Protection (IP65) (dust-tight and jet-water-protected) //

TECHNICAL DATA:

Display:	6000 Counts
Measuring method:	True RMS
Voltage measurement:	AC/DC
Measuring range V/DC:	0.1 mV - 1000 V
Measuring range V/AC:	0.1 mV - 750 V
Basic accuracy:	±0.7 %
Frequency range:	40 Hz - 400 Hz
DC/AC internal resistance:	10 MΩ
Current measurement:	AC/DC
Measuring range A/DC:	0.1 μA - 10 A (20 A)
Measuring range A/AC:	0.1 μA - 10 A (20 A)
Measuring range resistance:	0.1 Ω - 60 MΩ
Measuring range frequency electronic:	600 Hz - 40 MHz (approx. 30 Vrms)
Measuring range frequenz electrical:	40 - 400 Hz (sensitivity >30 Vrms)
Measuring range capacity:	0.001 nF - 60 mF
Measuring range temperature:	-40 to +1000 °C
3-Phase rotating direction display:	right turning/left turning
Measuring category:	CAT III 1000 V, CAT IV 600 V
Degree of contamination:	2
Safety according to:	EN61010-1
Protection type:	IP65 (dust-tight and jet-water-protected)
Voltage supply:	9 V block
Product dimensions (L x W x H):	195 x 95 x 58 mm
Weight:	approx. 473 g



EQUIPMENT:

Standard measurement functions: V-AC/DC, LoZ V/AC, A-AC/DC, resistance, diode test, capacitance, frequency, temperature // Acoustic continuity test // Data hold // Relative measuring function // Max/min memory // Auto range/manual range // Automatic power-off (can be disabled) // Battery condition indicator // Automatic backlight (can be disabled) // Integrated LED lamp // 3-phase rotation test with 2 leads //

PACKAGE CONTENTS:

Digital multimeter // Type K thermal sensor with adapter // 2x CAT IV safety test leads // 9 V block battery // Safety instructions // Operating instructions (on CD) //

Legal notice

This data sheet is published by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data sheet represent the technical status at the time of printing.

© Copyright 2022 by Conrad Electronic SE

1500207_V5_1221_01_PIX_ds