

KERN CCS30K0.01.

Zählsystem zum Zählen kleinster Teile in großen Mengen, Zählauflösung bis zu 999.999 Punkte



Measuring system

Adjustment options:	External calibration
Linearity:	50 mg
Recommended adjusting weight:	30000 g (M1)
Reproducibility:	20 mg
Weighing system:	Strain gauge
Weighing units:	kg lb

Display

Display digit height:	2 cm
-----------------------	------

Counting

Counting resolution:	600000
Minimum piece weight at piece counting (Laboratory):	50 mg
Minimum piece weight at piece counting (Normal):	500 mg
Reference weight:	yes

Functions

Conversion function:	yes
Counting function:	yes
Function to save totals:	yes
PRE-TARE function:	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	0 %

Power supply

Charging time:	12 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK US
Operating time (Backlight on):	70 h
Rechargeable battery:	Rchrg. battery optional

Service

Adjustment at the location of installation: abhängig von Auflösung/Max | depends on resolution and capacity

DAkkS Certificate: 962-128-127

Category

Brand:	KERN
Product Group:	Counting system

Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	950 x 650 x 240 mm
Gross weight:	15,900 kg
Net weight:	12,050 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	2,500 m
Casing material:	Plastic
Dimensions of weighing plate (WxDxH):	400 x 300 x 128 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	320 x 330 x 125 mm
Revolving screw feet:	yes
Weighing surface (WxD):	400 x 300 mm