

### Data Sheet

**Type Number** ..... 20393  
**Designation IEC** ..... SR754W (SR48)  
**System** ..... Silver Oxide / Zinc / KOH - Electrolyte




**Nominal Voltage** ..... 1,55 V  
**Typical Capacity C** ..... 77 mAh  
 Load 13 kOhm, at 20°C down to 1.2 V

**Weight (approx.)** ..... 1,02 g  
**Volume** ..... 0,24 ccm  
**Coding**..... Date of Manufacturing Month/Year

**Temperature Ranges**

	min	max.
Storage .....	0°C	60°C
Discharge .....	0°C	60°C*



**Dimensions**

	min	max.
Diameter (A) .....	7,55	7,90
Height (B) .....	5,00	5,40
Shoulder Diameter[E].....	3,50	
Shoulder Height [C].....	0,08	

### Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	1.2 V
Continuous	13000 Ω	Time:	660 h
24h/d, 7d/w		Capacity [mAh]:	77
Current [μA]:		Energy [mWh]:	114

\* Contact if the application is intended to be outside the range of 0°C to +60°C.

*Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice.*