



Discover more details and matching accessories online!

Parcel scales with big platform for fast and easy weighing in the office, production, dispatch etc.

Features

- Thanks to battery operation, compact, light-weight construction, it is suitable for the use in several locations
- Wall mount for display device, standard
- Hold function: When the weighing conditions are unstable, a stable weight is calculated determining an average value

Technical data

- Large LCD display, digit height 25 mm
- Weighing platform dimensions, steel, lacquered
 - A** W×D×H 315×305×57 mm
 - B** W×D×H 550×550×58 mm, see larger picture
 - C** W×D×H 950×500×58 mm
- Dimensions of display device W×D×H 235×114×51 mm
- Optional battery operation, 4×1.5 V AA not included in scope of delivery, operating time up to 100 h
- Permissible ambient temperature 5 °C/35 °C

STANDARD



OPTION



Model	Weighing capacity [Max] kg	Readability [d] g	Reproducibility g	Linearity g	Net weight approx. kg	Weighing plate	Options
							Calibr. Certificate DAkks accr. KERN
KERN							
EOE 10K-3	15	5	5	± 10	4,0	A	963-128
EOE 30K-2	35	10	10	± 20	4,0	A	963-128
EOE 60K-2	60	20	20	± 40	4,0	A	963-129
EOE 60K-2L	60	20	20	± 40	14	B	963-129
EOE 100K-2	150	50	50	± 100	4,0	A	963-129
EOE 150K50L	150	50	50	± 100	14	B	963-129
EOE 150K50XL	150	50	50	± 100	18	C	963-129
EOE 300K100	300	100	100	± 200	4,0	A	963-129
EOE 300K100L	300	100	100	± 200	14	B	963-129
EOE 300K100XL	300	100	100	± 200	18	C	963-129