

SAIEW-M8S-4S-H12TL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 1429-0

Fax: +49 5231 14292083

www.weidmueller.com

Similar to illustration

Weidmüller is now one of the industry's leading international providers of connectors. An important mainstay in this product family are the circular connectors, which Weidmüller groups under the product name SAI. In the development of SAI products, Weidmüller engineers have always concentrated on achieving rational, cost-effective installation concepts, and – in cooperation with major users – have supplied the markets with well-conceived products which set standards in terms of functionality and quality across the globe. The best examples are the new power distributors with S and T coded M12. These modules are characterised by particularly high currents and voltages. This enables them to also be used, for example, with three-phase motors.

General ordering data

Type	SAIEW-M8S-4S-H12TL
Order No.	2424450000
Version	Built-in plugs, M8, No. of poles: 4
GTIN (EAN)	4050118430646
Qty.	10 pc(s).

SAIEW-M8S-4S-H12TL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 1429-0

Fax: +49 5231 14292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	12.9 g
------------	--------

Technical data of PCB plug-in connector

Coding	M8 = none	Mounting thread	Pin: M8 / Socket: M12
No. of poles	4	Type of mounting	Rear panel mounting
Rated voltage		Rated voltage (text)	60 V (3-pole) / 30 V (4-pole)
	30 V	Rated current	4 A
Rated current	4 A	Protection degree	IP67
Temperature range	-30...+80 °C	Housing main material	CuZn, nickel-plated
Contact surface	Au (Gold)	Tightening torque	M8: 0.5 Nm
connection thread	M8	Mounting torque range	1.2 Nm
Mounting thread	M8	Pollution severity	3 (2 within the sealed area)
Insulation resistance		Contact material	CuZn
	100 MΩ	Lock nut material	Nickel-plated CuZn
Plugging cycles	≥ 100	Grouting material	PUR
Seal material	NBR		
Material of the flange-mounted housing	Nickel-plated CuZn		

Material data

Contact material	CuZn	Contact surface	Au (Gold)
------------------	------	-----------------	-----------

System parameters

Insulation resistance	100 MΩ	No. of poles	4
Pin series quantity	1	Plugging cycles	≥ 100
Protection degree	IP67		

Classifications

ETIM 6.0	EC002638	eClass 6.2	27-26-07-02
eClass 9.1	27-44-03-09		

Approvals


ROHS	Conform
------	---------

SAIEW-M8S-4S-H12TL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com


Drawings

Dimensioned drawing




L(board-to-board distance) = 12mm

PCB design



Pole scheme



M8 = none