

KERN PES620-3M



Robuste Labor- und Industrie-Präzisionswaage für schweres Wägegut, mit Eichzulassung [M]



Measuring system

Adjustment options:	External calibration
Linearity:	3 mg
n/a:	2 g
Readout [d]:	1 mg
Recommended adjusting weight:	500 g (E2)
Reproducibility:	1 mg
Resolution:	620000
Stabilisation time:	3 s
Warm up time:	4 h
Weighing range [Max]:	620 g
Weighing units:	ct g kg

Display

Display digit height:	1,400 cm
-----------------------	----------

Technical data about verification

Verification approval conforming to 2014/31/EU:	yes
---	-----

Counting

Counting resolution:	620000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg

Functions

Counting function:	yes
Function to save totals:	yes
Percentage determination:	yes
Standby function:	yes
Suspended weighing:	Loop
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	30 °C
Minimum ambient temperature:	10 °C

Power supply

Charging time:	15 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	32 h
Operating time (Backlight on):	6 h
Rechargeable battery:	Rchrg. battery optional

Service

DAkkS Certificate:	963-127
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	335 x 435 x 220 mm
Gross weight:	5,120 kg
Net weight:	3,760 kg
Shipping method:	Parcel service

KERN PES620-3M



Robuste Labor- und Industrie-Präzisionswaage für schweres Wägegut, mit Eichzulassung [M]

Construction

Casing material:	Cast aluminium alloys
Dimensions draft shield (WxDxH):	175 x 155 x 105 mm
Dimensions housing (WxDxH):	220 x 330 x 90 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing space (WxDxH):	170 x 150 x 100 mm
Weighing surface (WxD):	140 x 120 mm