

WS
WS 12/6 MM WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 1429-0

Fax: +49 5231 14292083

www.weidmueller.com

**WS/ DEK**

MultiMark DEK/WS connector markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Compatible with W, Z, P and SAK series terminal blocks
- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Space for multi-line printing

General ordering data

Type	WS 12/6 MM WS
Order No.	2007200000
Version	WS, Terminal marker, 12 x 6 mm, Weidmueller, White
GTIN (EAN)	4050118391886
Qty.	600 pc(s).

WS

WS 12/6 MM WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	12 mm	Length (inches)	0.472 inch
Width	6 mm	Width (inches)	0.236 inch
Net weight	0.14 g		

General data

Application/manufacture	Weidmueller	Colour	White
Length	12 mm	Material	PC-ABS, TPU
Number per roll	600	Operating temperature range, max.	90 °C
Operating temperature range, min.	-50 °C	UL 94 flammability rating	V-2
Version	with clip-in foot, halogen-free	Width	6 mm

Classifications

ETIM 6.0	EC000761	eClass 6.2	27-14-11-37
eClass 9.0	27-14-11-37	eClass 9.1	27-14-11-37

Approvals

ROHS	Conform
------	---------

Downloads

Engineering data	EPLAN, Zuken E3.S
------------------	-----------------------------------