

LTE GSM Modem HT CAT 4



LTE GSM Modem for wireless data transfer
(RS232, USB or LAN)

Order no.: 700600250S (RS232-Version)
Order no.: 700600260S (USB-Version)
Order no.: 700600270S (LAN-Version)

Applications

Data transmission out of:

- distance measurement applications
- SPS controlled applications
- PC systems
- RAS applications
- Vending machines
- Air power applications



General informations

Standard interfaces for industrial applications and integrated SIM card reader makes the LTE GSM Quadband Modem a right LTE GSM terminal solution for several applications in wireless data. It allows the quick realisation of applications in the telemetry and telematic.

Conditions

To use the LTE GSM Modem you need:
PC with RS232, USB or LAN-interface, Antenne, SIM-card with data activation (prepaid or fix contract)

Technical specific features

- Available with RS232, USB (Bus-powered) or LAN
- Usable with Windows and Linux systems
- Using all LTE/GSM services (voice (voice call without voice transmission possible), data, tele.)
- Using in european LTE/GSM networks (other regions on request)
- IP with TCP and UDP, FTP, SMTP, SMS
- Small dimensions for simple integration in applications

Technical data

GSM networks	GSM 800 + 900 + 1800 + 2100 + 2600 MhZ	AT-Commands	3 GPP rel.9 compliant, 3 GPP TS 51.014 (SIM), Standard- and extended AT Commands	
Data rate	50 Mbps Up, 100 Mbps Down (LTE CAT 4) 5.76 Mbps Up, 42.0 Mbps Down (HSPA+)	Interfaces	LAN, USB oder Rs232, D-SUB 9 female	
Approval	CE, GCF (Europe)	Aerial	SMA, 50 Ohm	
Physical dimensions/ weight	75 x 22 x 112mm (L x B x H) / 92 g	Scope of supply	LTE GSM Modem Manual CD with Software	
Temperature range	- 40 °C bis + 65 °C working temperature	Optional accessories	Power supply for DIN rail mounting 230 V AC / 12 V DC Glass Attached Antenna (Indoor use), 1,5 m cable (SMA) Round Antenna PUK (Indoor and Outdoor use), 3 m cable (SMA)	Order-No. 700100302 300303304S 300303310S
Power supply	9-35 V DC (LAN, RS232), BUS powered (USB)			
Power consumption	9 V (middle 250 mA, peak 1000 mA), 12 V (middle 180 mA, peak 750 mA), 24 V (middle 100mA, peak			