# Mounting flange




### **Model Number**

#### BF 30-F

Mounting flange with dead stop, 30 mm

#### **Features**

- Black plastic housing with dead stop for all cylindrical sensors with M30 thread
- Easy sensor replacement via fixing flap in the top of the fixing flange
- Embeddable sensors lie flush with the surface of the fixing flange
- The cap of a non-embeddable sensor protrudes through the fixing flange. This allows non-embeddable sensors to be easily mounted on metal surfaces.
- max. 8 mm range of adjustment is provided for the positioning of the flange by means of the elongated holes on the side



			÷
Dead stop			
4.2			
	€ <b>∃</b>	∋i⊂	÷
		4.1	
		7.	8
-		14	
	-		

30 mm

## **Technical data**

**General specifications** 

Inside diameter

- Ambient conditions
- Ambient temperature
- **Mechanical specifications** Material

-25 ... 85 °C (248 ... 358 K)

Polycarbonate (PC), black

## Note Installation

- · Position the mounting bracket on the desired place
- Mark the position of drilling holes in the mid section of the oblong holes
- ٠ Drill the mounting holes through the surface
- Screw on the mounting bracket slightly via the lateral oblong holes by using suitable M4 screws
- Stick the sensor through the mounting bracket and fix the sensor by the lid on the upper part of the bracket
- Adjust the bracket and make the final positioning
- · Fix the mounting bracket finally with the screws

Copyright Pepperl+Fuchs, Printed in Germany