







## **Model Number**

#### UBE800-F77-SE3-V31

Through-beam ultrasonic barrier

## Features

- · Miniature design
- Highly visible LEDs for Power ON and switching state
- · High switching frequency
- Program input
- · Degree of protection IP67

### **Technical data**

General specifications	
Sensing range	0 800 mm emitter/receiver spacing
04	4-6-1-

Standard target plate see table
Transducer frequency approx. 300 kHz

 $\label{eq:local_problem} \mbox{Nominal ratings} \\ \mbox{Time delay before availability } \mbox{t}_{\mbox{\scriptsize V}} & \leq 150 \mbox{ ms} \\ \mbox{}$ 

Limit data

Permissible cable length max. 300 m

Indicators/operating means

LED green Power on ( emitter )
LED yellow switching state ( receiver )

Electrical specifications
Rated operating voltage U<sub>a</sub> 24 V DC

Operating voltage  $U_B$  20 ... 30 V DC , ripple 10  $\%_{SS}$  ; 12 ... 20 V DC sensitivity

reduced to 80 %

No-load supply current  $I_0 \le 20 \text{ mA}$ 

Input
Input type 1 program input (receiver)

Level low level : 0 ... 0.7 V; high level : > 14 V

 $\begin{array}{ll} \text{Input impedance} & 16 \text{ k}\Omega \\ \text{Pulse length} & \geq 3 \text{ s} \end{array}$ 

Output
Output type 1 switch output PNP , NC contact

Rated operating current  $I_e$  200 mA , short-circuit/overload protected Voltage drop  $U_d$   $\leq$  2 V

 Ambient conditions

 Ambient temperature
 -25 ... 70 °C (-13 ... 158 °F)

 Storage temperature
 -40 ... 85 °C (-40 ... 185 °F)

Shock resistance 30 g , 11 ms period
Vibration resistance 10 ... 55 Hz , Amplitude ± 1 mm

Mechanical specifications

Connection type M8 x 1 connector , 4-pin

Degree of protection IP67

Material
Housing Polycarbonate

Transducer epoxy resin/hollow glass sphere mixture; polyurethane foam

Installation position

Mass
Per 10 g

Tightening torque, fastening screws

max. 0.2 Nm

Compliance with standards and

directives

Standard conformity
Standards
EN 60947-5-2:2007 + A1:2012

IEC 60947-5-2:2007 + A1:2012


Approvals and certificates

UL approval cULus Listed, General Purpose
CSA approval cCSAus Listed, General Purpose

CCC approval / marking not required for products rated


≤36 V

# **Dimensions**




# **Electrical Connection**

Receiver:



Emitter:



# **Pinout**

2



PEPPERL+FUCHS

Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

## **Accessories**

#### OMH-ML7-01

Mounting aid for ML7 and ML8 series, Mounting bracket

#### V31-GM-2M-PVC

Female cordset, M8, 4-pin, PVC cable

### V31-WM-2M-PVC

Female cordset, M8, 4-pin, PVC cable

### **Description of Sensor Function**


An ultrasonic thru-beam sensor always consists of an ultrasonic emitter and receiver. The working principle of the ultrasonic thru-beam sensor is based on the interruption of the transmission from the emitter to the receiver by the object to be detected (obstacle).

The emitter produces an ultrasonic signal which is evaluated by the receiver. If the signal is damped or broken by the object being detected, the receiver switches state.

No electrical connections are required between the emitter and receiver.

### Sensitivity adjustment

The sensitivity is adjusted using the input ET. This can be open or connected using +UB or -UB.



ET	Sensitivity	D	B <sup>(1)</sup>	L <sup>(1)</sup>
Open	High	≤ 800 mm	≥ 50 mm	≥ 15 mm
-U <sub>B</sub>	Medium	<u>&lt;</u> 600 mm	≥ 40 mm	≥ 10 mm
+U <sub>R</sub>	Low	< 400 mm	≥ 30 mm	≥ 5 mm

(1) The specified values for B and L are reference values and refer to the maximum distance D and to objects with a rectangular shape. The shape of the objects can have an effect on the values for B and L.

# **Safety Note**



The use of this device in applications, where the safety of persons depends from the devices function, is not allowed!