



# ZKHZ.E239003 - Machine-tool Wire

## Machine-tool Wire

**Helu Kabel GmbH**

Schlosshaldenstrasse 10  
Hemmingen, 71282 Germany

E239003

Types(s) MTW

Last Updated on 2021-07-10

---

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2021 UL LLC"

# AVLV2.E170315 - Appliance Wiring Material - Component

## Appliance Wiring Material - Component

### Helu Kabel GmbH

Schlosshaldenstrasse 10  
Hemmingen, 71282 Germany

E170315

### Table of Recognized Styles

Single-conductor, thermoplastic insulation							
1002	1195	1473	1638	1953	10449	10729	11108
1007	1200	1475	1647	1967	10456	10737	11113
1010	1207	1477	1650	1972	10467	10750	11117
1011	1208	1478	1662	1973	10483	10752	11118
1013	1211	1479	1672	1976	10484	10754	11120
1015	1218	1480	1674	1992	10489	10764	11122
1017	1226	1482	1675	1994	10492	10767	11134
1019	1227	1483	1679	1998	10493	10768	11146
1020	1233	1484	1680	10002	10522	10770	11170
1021	1235	1490	1683	10008	10530	10771	11179
1022	1237	1497	1685	10012	10532	10774	11211
1023	1239	1498	1691	10037	10533	10775	11212
1024	1241	1499	1692	10042	10539	10794	11213
1026	1249	1500	1694	10053	10540	10795	11214
1027	1252	1508	1723	10059	10541	10796	11215
1028	1253	1509	1728	10062	10542	10797	11216
1030	1265	1510	1729	10070	10545	10798	11217
1032	1266	1513	1730	10071	10553	10799	11295
1037	1283	1516	1731	10097	10557	10800	11304
1039	1284	1517	1732	10104	10559	10801	11321
1049	1304	1523	1747	10107	10572	10856	11324
1054	1314	1533	1748	10108	10578	10857	11445
1061	1316	1534	1758	10113	10579	10858	11482

1063	1330	1538	1759	10124	10585	10867	11635
1095	1331	1557	1761	10127	10586	10921	11641
1099	1332	1568	1762	10131	10587	10924	11657
1107	1333	1569	1763	10138	10593	10925	11658
1108	1335	1571	1777	10140	10599	10946	11659
1109	1336	1575	1781	10152	10602	10954	11660
1110	1337	1576	1783	10198	10615	10958	11896
1113	1345	1577	1787	10221	10623	10965	11897
1114	1347	1581	1788	10232	10627	10974	11898
1115	1349	1582	1792	10236	10631	10975	11899
1116	1354	1583	1800	10258	10643	10981	11900
1117	1365	1586	1828	10263	10645	10982	11901
1118	1366	1589	1829	10264	10646	10983	11913
1119	1371	1591	1836	10269	10651	10988	11914
1120	1375	1592	1840	10271	10666	10989	11937
1121	1386	1598	1856	10280	10675	10994	11938
1122	1429	1600	1890	10324	10678	10995	11941
1123	1430	1605	1903	10340	10680	10997	11942
1124	1431	1609	1920	10346	10681	10998	11943
1146	1435	1610	1921	10347	10682	11008	11952
1148	1436	1617	1922	10356	10683	11009	
1149	1437	1618	1929	10368	10684	11010	
1150	1438	1626	1930	10387	10699	11034	
1160	1439	1627	1940	10390	10705	11035	
1161	1444	1631	1943	10438	10707	11037	
1162	1447	1637	1950	10446	10708	11107	
<b>Multiple-conductor, thermoplastic insulation</b>							
2089	2405	2678	20175	20668	21153	21324	21633
2090	2448	2697	20187	20669	21156	21325	21634
2091	2450	2698	20188	20671	21161	21327	21694
2092	2461	2704	20194	20689	21164	21328	21695
2093	2462	2709	20195	20692	21165	21329	21697
2094	2463	2725	20196	20724	21169	21330	21698

2095	2464	2726	20197	20745	21170	21338	21706
2096	2468	2738	20200	20773	21173	21339	21707
2097	2481	2739	20201	20789	21178	21344	21743
2098	2482	2740	20207	20841	21179	21349	21744
2099	2483	2785	20233	20844	21183	21350	21753
2100	2487	2786	20234	20850	21184	21353	21754
2101	2490	2789	20235	20851	21188	21356	21755
2102	2493	2790	20236	20855	21198	21364	21756
2103	2494	2791	20251	20866	21209	21369	21757
2112	2498	2818	20254	20870	21216	21370	21758
2113	2501	2833	20255	20882	21217	21371	21781
2114	2502	2835	20256	20886	21218	21379	21782
2115	2516	2839	20276	20910	21222	21381	21840
2116	2517	2841	20279	20911	21223	21387	21887
2117	2530	2842	20280	20913	21235	21390	21907
2118	2532	2844	20281	20917	21238	21397	21925
2121	2535	2854	20306	20921	21241	21409	21926
2122	2549	2863	20317	20936	21254	21437	21927
2123	2550	2879	20318	20939	21264	21439	21947
2124	2551	2885	20327	20940	21265	21446	22009
2125	2552	2892	20330	20950	21266	21448	22010
2126	2555	2905	20350	20954	21270	21449	22022
2127	2560	2912	20351	20963	21271	21451	22048
2128	2561	2919	20352	20968	21273	21452	22066
2129	2562	2920	20353	20979	21274	21453	22079
2133	2570	2931	20379	21002	21279	21454	22080
2134	2571	2934	20403	21025	21280	21455	22083
2165	2574	2935	20405	21026	21281	21456	22100
2166	2576	2936	20410	21027	21282	21468	22148
2243	2582	2960	20411	21029	21283	21469	22176
2244	2584	2969	20413	21030	21286	21472	22177
2245	2586	2990	20417	21047	21287	21473	22178
2246	2587	20002	20420	21060	21288	21474	22179

2284	2589	20009	20432	21061	21292	21475	22180
2285	2598	20058	20433	21064	21293	21476	22221
2286	2610	20060	20438	21088	21294	21481	22222
2287	2614	20063	20450	21089	21303	21484	22223
2288	2626	20066	20464	21096	21304	21491	22230
2321	2630	20084	20475	21098	21305	21492	22231
2338	2631	20096	20479	21099	21306	21502	22232
2343	2637	20097	20549	21100	21307	21513	22233
2344	2651	20098	20554	21103	21309	21529	22234
2345	2653	20099	20563	21104	21313	21530	22235
2346	2654	20106	20601	21118	21314	21535	22236
2348	2655	20126	20603	21120	21315	21566	22237
2384	2656	20127	20605	21127	21316	21573	
2385	2660	20128	20607	21130	21317	21576	
2386	2661	20129	20608	21132	21318	21611	
2387	2662	20130	20621	21143	21320	21612	
2388	2665	20131	20622	21144	21322	21631	
2397	2668	20170	20626	21151	21323	21632	
<b>Single-conductor, thermoset insulation</b>							
3135	3271	3315	3393	3469	3644	3814	
3173	3272	3317	3409	3475	3646	3920	
3182	3275	3352	3415	3482	3666	3995	
3195	3296	3376	3423	3529	3676	3996	
3237	3302	3385	3443	3558	3697	3997	
3266	3314	3386	3450	3578	3773	30094	
<b>Multiple-conductor, thermoset insulation</b>							
4476	4535						

Marking: Company name, voltage rating, temperature rating, conductor size, conductor material if other than copper,.

Last Updated on 2021-10-04

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2021 UL LLC"