



VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“For more than 25 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

P9-4

9V BATTERY CHARGER

Nº 1527210

CE

VERSION 02/17

This charger is designed for charging, discharging, refreshing and testing of up to four 9 V rechargeable batteries. It features 4 charging bays, that work independently of one another. You can therefore use different rechargeable batteries at the same time. The product has the minus delta-V function which monitors voltage during charging. As soon as NiMH and NiCd rechargeable batteries are fully charged, the product switches automatically to trickle charge. Power supply is via the mains supply unit included in delivery.

HIGHLIGHTS

Suitable for rechargeable NiMH, NiCd and Li-ion batteries //

Functions: charging, discharging, testing, refreshing, quick test //

Individual monitoring of each charging slot //

LCD: voltage, current, capacity, time, resistance //

Reverse polarity protection //

Short circuit protection //



TECHNICAL DATA

Charger	
Operating voltage	12 V/DC
Charging current	50 - 200 mA (adjustable in steps of 25 mA)
Suitable rechargeable battery types	NiMH, NiCd, Li-ion
Rechargeable battery voltage	7.2 / 8.4 / 9.6 V
Operating conditions	0 to +45 °C, 1 - 90 % RH
Storage conditions	-20 to +60 °C, 1 - 90 % RH
Dimensions (W x H x D)	120 x 30 x 95 mm
Weight	139 g
Power adapter	
Input voltage	100 - 240 V/AC, 50/60 Hz
Output voltage/current	12 V/DC, 1.5 A
Protection class	II
Cable length	1.4 m
Weight	93 g

PACKAGE CONTENT

9V battery charger // Power adapter // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.