

High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



High-current terminal block, Blocked, Connection method: Power-Turn connection, Number of connections: 10, Cross section: 10 mm² - 70 mm², AWG: 8 - 2/0, Width: 100 mm, Color: gray/blue/black-yellow, Mounting type: NS 35/15

Your advantages

- ✓ Quick and easy connection is now also possible for large conductors with the high-current terminal block
- ✓ The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- ✓ The compact design enables wiring in a confined space
- ✓ In addition to using the existing test connection, pick-off terminal blocks can be connected, each of which can also accommodate two test cables

Key commercial data

package_quantity	2
GTIN	4046356998703

Technical data

General

Number of levels	1
Number of connections	10
Potentials	1
Nominal cross section	50 mm ²
Color	gray/blue/black-yellow
Insulating material	PA
Flammability rating according to UL 94	V0

General

Rated surge voltage	8 kV
Degree of pollution	3
Overvoltage category	III
Insulating material group	I
Maximum power dissipation for nominal condition	4.73 W
Maximum load current	150 A (with 50 mm ² conductor cross section)
Nominal current I _N	150 A
Nominal voltage U _N	1500 V
Open side panel	No

High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Technical data

General

Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Static insulating material application in cold	-60 °C
Behavior in fire for rail vehicles (DIN 5510-2)	Test passed
Flame test method (DIN EN 60695-11-10)	V0
Oxygen index (DIN EN ISO 4589-2)	>32 %
NF F16-101, NF F10-102 Class I	2
NF F16-101, NF F10-102 Class F	2
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Calorimetric heat release NFPA 130 (ASTM E 1354)	27,5 MJ/kg
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

Dimensions

Width	100 mm
Length	101 mm
Height NS 35/15	105 mm

Connection data

Connection method	Power-Turn connection
Connection in acc. with standard	IEC 60947-7-1
Conductor cross section solid min.	10 mm ²
Conductor cross section solid max.	70 mm ²
Conductor cross section AWG min.	8
Conductor cross section AWG max.	2/0
Conductor cross section flexible min.	10 mm ²
Conductor cross section flexible max.	70 mm ²
Min. AWG conductor cross section, flexible	8
Max. AWG conductor cross section, flexible	2/0
Conductor cross section flexible, with ferrule without plastic sleeve min.	10 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	50 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve min.	10 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve max.	50 mm ²
Cross section with insertion bridge solid min.	10 mm ²

High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Technical data

Connection data

Cross section with insertion bridge, solid max.	50 mm ²
Cross section with insertion bridge stranded min.	10 mm ²
Cross section with insertion bridge, stranded max.	50 mm ²
Cross section with insertion bridge stranded, with ferrule without plastic sleeve min.	10 mm ²
Cross section with insertion bridge stranded, with ferrule without plastic sleeve max.	50 mm ²
Cross section with insertion bridge stranded, with ferrule without plastic sleeve min.	10 mm ²
Cross section with insertion bridge stranded, with ferrule with plastic sleeve max.	50 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	10 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	16 mm ²
Cross section with insertion bridge, solid max.	50 mm ²
Cross section with insertion bridge, stranded max.	50 mm ²
Stripping length	30 mm
Internal cylindrical gage	A10

Standards and Regulations

Connection in acc. with standard	IEC 60947-7-1
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
China RoHS	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 8.0	27141120
eCl@ss 9.0	27141120

ETIM

ETIM 5.0	EC000897
ETIM 6.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Approvals

CSA / UL Recognized / cUL Recognized / DNV GL / LR / BV / cULus Recognized /

Approval details

CSA ®		
Usegroups	B	C
Nominal voltage UN	600 V	1000 V
Nominal current IN	140 A	140 A
mm²/AWG/kcmil	8-1/0	8-1/0

UL Recognized	
Nominal voltage UN	1000 V
Nominal current IN	140 A
mm²/AWG/kcmil	8-1/0

cUL Recognized	
Usegroups	C
Nominal voltage UN	1000 V
Nominal current IN	140 A
mm²/AWG/kcmil	8-1/0

DNV GL

LR UL Recognized

BV ®

cULus Recognized ULus

Accessories

Pick-off terminal block

AGK 10-PTPOWER - 3260145



High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Accessories

AGK 10-PTPOWER BU - 3260148



AGK 10-PTPOWER GN/YE - 3260151



AGK 10-PTPOWER BK/YE - 3260154



Screwdriver tools

SZF 3-1,0X5,5 - 1206612



Test plug terminal block

PS-MT - 0311647



High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Accessories

MPS-MT - 0201744



MPS-MT/ 4MM - 3048577



Insulating sleeve

PS-IH RD - 0311579



MPS-IH WH - 0201663



MPS-IH RD - 0201676



High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Accessories

MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



MPS-IH WH - 0201663



High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Accessories

MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Accessories

MPS-IH BK - 0201731



Insertion bridge

EB 2-20/PT - 3260067



EB 3-20/PT - 3260068



DIN rail

NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Accessories

NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Accessories

NS 35/15 CAP - 1206573



End block

E/AL-NS 35 - 1201662



Terminal marking

TMT 10 R - 0816210



ZB 10:UNBEDRUCKT - 1053001



UC-TM 10 - 0818069



High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Accessories

UCT-TM 10 - 0829142



ZBF10:UNBEDRUCKT - 0809997



UC-TMF 10 - 0818124



UCT-TMF 10 - 0829204



Labeled terminal marker

TMT 10 R CUS - 0824500



High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Accessories

ZB 10 CUS - 0824941



ZB10,LGS:FORTL.ZAHLEN - 1053014



ZB10,QR:FORTL.ZAHLEN - 1053027



ZB10,LGS:GLEICHE ZAHLEN - 1053030



ZB10,LGS:L1-N,PE - 1053412



ZB10,LGS:U-N - 1053438



High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Accessories

UC-TM 10 CUS - 0824605



UCT-TM 10 CUS - 0829623



ZBF10 CUS - 0825031



ZBF10,LGS:FORTL.ZAHLEN - 0810009



ZBF10,QR:FORTL.ZAHLEN - 0810025



High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Accessories

UC-TMF 10 CUS - 0824662



UCT-TMF 10 CUS - 0829679



Planning and marking software

CLIP-PROJECT ADVANCED - 5146040



CLIP-PROJECT PROFESSIONAL - 5146053



Connector

A 25 -40 - 3241238



High-current terminal block - PTPOWER 50-3L/N/FE - 3260056

Accessories

A 35 -40 - 3241239



A 50 -40 - 3241240



A 70 -40 - 3241241




A 95 -40 - 3241242



Drawings

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>