

## Coaxial Cable Connector 11\_BNC-50-2-14/133\_N

### Description

Straight cable plug

Interface standards

IEC 60169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 4 GHz

#### Mechanical Data

Centre contact crimped  
Outer 2contact crimped  
Weight 0.0098 kg

#### Environmental Data

Operating temperature -65 °C to 165 °C  
2011/65/EU (RoHS) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	

### Related Documents

Outline drawing DOU-00006663  
Catalogue drawing DOU-00006199  
Assembly instruction DOC-0000179123

### Ordering Information

Single package 11\_BNC-50-2-14/133\_NE  
Bulk 100 pcs package 11\_BNC-50-2-14/133\_NH

### Additional Information

Suitable cables K\_02252\_D, ENVIROFLEX\_316\_D, G\_02232\_D