

Within Series Adaptor 32_SK-50-0-1/199_N

Description

Adaptor plug/plug
SK plug (male) / SK plug (male)

For Test & Measurement applications
Precision adaptor

Interface standard
Series SK - MIL-STD-348A/323



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	40 GHz
Frequency range	DC to 40 GHz
Return loss	≥ 20 dB
Electrical length	16.1 mm

Mechanical Data

Number of matings	500
Weight	0.0061 kg

Environmental Data

Operating temperature	-40 °C to 125 °C
2011/65/EU (RoHS)	compliant

Material Data

Interface - SK plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Nickel Alloy	
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	
Coupling nut	Stainless Steel	

Interface - SK plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Nickel Alloy	
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	
Coupling nut	Stainless Steel	

Ordering Information

Single package	32_SK-50-0-1/199_NE
----------------	---------------------