

Mini feed-through terminal block - MPT 1,5/S - 3248100

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Mini feed-through terminal block, Connection method: Push-in connection, Number of connections: 2, Cross section: 0.14 mm² - 1.5 mm², AWG: 26 - 14, Width: 3.5 mm, Color: gray, Mounting type: NS 15

Your advantages

- ✓ Space saving thanks to compact design and mounting option on a 15 mm DIN rail
- ✓ Clear arrangement thanks to marking of all terminal points
- ✓ Tested for railway applications



Key commercial data

package_quantity	50
GTIN	4046356768719

Technical data

General

Number of levels	1
Number of connections	2
Potentials	1
Nominal cross section	1.5 mm ²
Color	gray
Insulating material	PA
Flammability rating according to UL 94	V0
Area of application	Railway industry
Area of application	Machine building
Area of application	Plant engineering

General

Rated surge voltage	6 kV
Degree of pollution	3
Overvoltage category	III
Insulating material group	I
Maximum power dissipation for nominal condition	0.56 W
Maximum load current	17.5 A

Mini feed-through terminal block - MPT 1,5/S - 3248100

Technical data

General

Nominal current I_N	17.5 A
Nominal voltage U_N	500 V
Open side panel	Yes
Shock protection test specification	DIN EN 50274 (VDE 0660-514):2002-11
Back of the hand protection	guaranteed
Finger protection	guaranteed
Result of surge voltage test	Test passed
Surge voltage test setpoint	7.3 kV
Result of power-frequency withstand voltage test	Test passed
Power frequency withstand voltage setpoint	1.89 kV
Result of the test for mechanical stability of terminal points (5 x conductor connection)	Test passed
Result of bending test	Test passed
Bending test conductor cross section/weight	0.14 mm ² / 0.2 kg
Bending test conductor cross section/weight	1.5 mm ² / 0.4 kg
Tensile test result	Test passed
Conductor cross section tensile test	0.14 mm ²
Tractive force setpoint	10 N
Conductor cross section tensile test	1.5 mm ²
Tractive force setpoint	40 N
Result of tight fit on support	Test passed
Tight fit on carrier	NS 15
Setpoint	1 N
Result of voltage-drop test	Test passed
Requirements, voltage drop	≤ 3.2 mV
Result of temperature-rise test	Test passed
Short circuit stability result	Test passed
Conductor cross section short circuit testing	1.5 mm ²
Short-time current	0.18 kA
Result of aging test	Test passed
Ageing test for screwless modular terminal block temperature cycles	192
Result of thermal test	Test passed
Proof of thermal characteristics (needle flame) effective duration	30 s
Oscillation, broadband noise test result	Test passed
Test specification, oscillation, broadband noise	DIN EN 50155 (VDE 0115-200):2008-03
Test spectrum	Service life test category 2, bogie-mounted
Test frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$
ASD level	6.12 (m/s ²) ² /Hz
Acceleration	3.12 g
Test duration per axis	5 h

Mini feed-through terminal block - MPT 1,5/S - 3248100

Technical data

General

Test directions	X-, Y- and Z-axis
Shock test result	Test passed
Test specification, shock test	DIN EN 50155 (VDE 0115-200):2008-03
Shock form	Half-sine
Acceleration	30g
Shock duration	18 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Static insulating material application in cold	-60 °C
Behavior in fire for rail vehicles (DIN 5510-2)	Test passed
Flame test method (DIN EN 60695-11-10)	V0
Oxygen index (DIN EN ISO 4589-2)	>32 %
NF F16-101, NF F10-102 Class I	2
NF F16-101, NF F10-102 Class F	2
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

Dimensions

Width	3.5 mm
End cover width	2.2 mm
Length	33.55 mm
Height NS 15	28.1 mm

Connection data

Connection method	Push-in connection
Connection in acc. with standard	IEC 60947-7-1
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section AWG min.	26
Conductor cross section AWG max.	14
Conductor cross section flexible min.	0.14 mm ²
Conductor cross section flexible max.	1.5 mm ²
Min. AWG conductor cross section, flexible	26

Mini feed-through terminal block - MPT 1,5/S - 3248100

Technical data

Connection data

Max. AWG conductor cross section, flexible	14
Conductor cross section flexible, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	1.5 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve max.	1 mm ²
Stripping length	8 mm ... 10 mm
Internal cylindrical gage	A1 / B1

Standards and Regulations

Connection in acc. with standard	CSA
Connection in acc. with standard	IEC 60947-7-1
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
China RoHS	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27141121
eCl@ss 4.1	27141121
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120
eCl@ss 9.0	27141120

ETIM

ETIM 3.0	EC001329
ETIM 4.0	EC000902
ETIM 5.0	EC000897
ETIM 6.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Mini feed-through terminal block - MPT 1,5/S - 3248100

Approvals

IECEEx / ATEX / CSA / UL Recognized / cUL Recognized / GL / BV / DNV / VDE Zeichengenehmigung / EAC / EAC / cULus Recognized /

Approval details

IECEEx	
Nominal voltage UN	352 V
Nominal current IN	14.5 A
mm²/AWG/kcmil	0.14-1.5

ATEX 	
Nominal voltage UN	352 V
Nominal current IN	14.5 A
mm²/AWG/kcmil	0.14-1.5

CSA 			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	15 A	15 A	5 A
mm²/AWG/kcmil	26-14	26-14	26-14

UL Recognized 			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	15 A	15 A	5 A
mm²/AWG/kcmil	26-14	26-14	26-14

cUL Recognized 			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	15 A	15 A	5 A
mm²/AWG/kcmil	26-14	26-14	26-14

GL 
--

BV 
--

DNV 

Mini feed-through terminal block - MPT 1,5/S - 3248100

Approvals

VDE Zeichengenehmigung 	
Nominal voltage UN	500 V
Nominal current IN	17.5 A
mm²/AWG/kcmil	0.14-1.5

EAC 
--



cULus Recognized 

Accessories

End cover

D-MPT 1,5/S - 3248120



Screwdriver tools

SZF 0-0,4X2,5 - 1204504



ST-BW 0 - 1200135



Jumper

Mini feed-through terminal block - MPT 1,5/S - 3248100

Accessories

FBS 2-3,5 - 3213014



FBS 3-3,5 - 3213027



FBS 4-3,5 - 3213030



FBS 5-3,5 - 3213043



FBS 10-3,5 - 3213056



FBS 20-3,5 - 3213069



Mini feed-through terminal block - MPT 1,5/S - 3248100

Accessories

FBS 2-3,5 BU - 3213086



FBS 3-3,5 BU - 3213099



FBS 4-3,5 BU - 3213109



FBS 5-3,5 BU - 3213112



FBS 10-3,5 BU - 3213125



Mini feed-through terminal block - MPT 1,5/S - 3248100

Accessories

FBS 20-3,5 BU - 3213138



FBS 2-3,5 GY - 3213153



FBS 3-3,5 GY - 3213167



FBS 4-3,5 GY - 3213180



FBS 5-3,5 GY - 3213183



FBS 10-3,5 GY - 3213196



Mini feed-through terminal block - MPT 1,5/S - 3248100

Accessories

FBS 20-3,5 GY - 3213206



DIN rail

NS 15 UNPERF 2000MM - 1401695



NS 15 PERF 2000MM - 1401682



NS 15 AL PERF 2000MM - 1401763



NS 15 WH PERF 2000MM - 1204096

End block

Mini feed-through terminal block - MPT 1,5/S - 3248100

Accessories

CLIPFIX 15 - 3022263



Terminal marking

ZBF 3,5:UNBEDRUCKT - 0829392



UCT-TMF 3,5 - 0829486



Labeled terminal marker

ZBF 3,5 CUS - 0829394



ZBF 3,5,LGS:FORTL.ZAHLEN - 0801406



Mini feed-through terminal block - MPT 1,5/S - 3248100

Accessories

ZBF 3,5,QR:FORTL.ZAHLEN - 0801407



UCT-TMF 3,5 CUS - 0829644



Test plug terminal block

MPS-MT - 0201744



PS-3,5 - 3031010



PS-3,5/E - 3031012



Insulating sleeve

Mini feed-through terminal block - MPT 1,5/S - 3248100

Accessories

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



Mini feed-through terminal block - MPT 1,5/S - 3248100

Accessories

MPS-IH BK - 0201731



Planning and marking software

CLIP-PROJECT ADVANCED - 5146040



CLIP-PROJECT PROFESSIONAL - 5146053



Partition plate

DP PS-3,5 - 3031011



Drawings

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>