

# LITHIUM CELL/BATTERY TEST SUMMARY

IN ACCORDANCE WITH SUB-SECTION 38.3  
OF MANUAL OF TESTS AND CRITERIA



N/A = Not Applicable

<b>1. Name of cell / battery</b>
1307-0000 1S1P Rechargeable Li-Ion-Battery

<b>2. Manufacturer of cell / battery / product</b>	
Name	Ansmann AG
Address	Industriestr. 10, 97959 Assamstadt
Phone	+49 6294 4204-0
Email	info@ansmann.de
Website	www.ansmann.de

<b>3. Test laboratory of cell / battery / product</b>	
Name	Shenzhen Anbotek Compliance Laboratory Limited
Address	East of 4/F, Building A, Hourui No.3 Industrial Zone, Xixiang Street, Bao'an District, Shenzhen Ch
Phone	+86755-26066126
Email	service@anbotek
Website	www.anbotek.com

<b>4. ID-number and date</b>			
Unique test report identification number	18270BC10211901	Date of test report	19.08.2021

## DESCRIPTION OF CELL / BATTERY

<b>5. Mark the type of cell/battery with an "•"</b>			
<input type="radio"/> Lithium ion cell		Lithium metal cell	<input type="radio"/>
<input checked="" type="radio"/> Lithium ion battery		Lithium metal battery	<input type="radio"/>

<b>6. Parameters</b>	<b>Cell</b>	<b>Battery</b>
Mass in gram (g):		52,2
Lithium ion: Indicate watt-hour rating (Wh):		9,36
Lithium metal: Indicate lithium metal content in gram (g):		

<b>7. Physical description of cell / battery</b>
Lithium-Ion Cylindrical

# LITHIUM CELL/BATTERY TEST SUMMARY

IN ACCORDANCE WITH SUB-SECTION 38.3  
OF MANUAL OF TESTS AND CRITERIA



<b>Name of cell/battery</b> (taken from field 1)
1307-0000 1S1P Rechargeable Li-Ion-Battery

<b>8. Model numbers</b>
1307-0000, 1307-0000-520

## TESTS AND RESULTS

9. List of tests conducted and results - Mark N/A, pass or fail with an "•"	N/A	pass	fail
T1 - Altitude simulation	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T2 - Thermal Test	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T3 - Vibration	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T4 - Shock	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T5 - External Short Circuit	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T6 - Impact / Crush	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T7 - Overcharge	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T8 - Forced Discharge	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T6 - Impact Cell	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T8 - Forced Discharge Cell	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>

<b>10. Reference to assembled battery testing requirements</b>		
	N/A	<input type="checkbox"/>

<b>11. Reference to the revised edition of the Manual of Tests and Criteria used and to amendments thereto</b>
ST-SG-AC10-11-Rev.7

<b>12. The manufacture of the cell / battery is in accordance with the documented quality management system as required by the regulations.</b>
---

13. Place, Date	14. Title, Surname, First name	15. Company stamp and signature
Assamstadt	Testzentrum i.A. K.Gehring	Klaus Gehring <small>Digital unterschrieben von Klaus Gehring Datum: 2021.09.09 17:16:41 +02'00'</small>