

Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Mini feed-through terminal block, Connection method: Push-in connection, Number of connections: 2, Cross section: 0.14 mm² - 1.5 mm², AWG: 26 - 14, Width: 3.5 mm, Color: blue, Mounting type: NS 15

The illustration shows the version in gray

Your advantages

- ✓ Space saving thanks to compact design and mounting option on a 15 mm DIN rail
- ✓ Clear arrangement thanks to marking of all terminal points
- ✓ Tested for railway applications



Key commercial data

package_quantity	50
GTIN	4046356768702

Technical data

General

Number of levels	1
Number of connections	2
Potentials	1
Nominal cross section	1.5 mm ²
Color	blue
Insulating material	PA
Flammability rating according to UL 94	V0
Area of application	Railway industry
Area of application	Machine building
Area of application	Plant engineering

General

Rated surge voltage	6 kV
Degree of pollution	3
Overvoltage category	III
Insulating material group	I
Maximum power dissipation for nominal condition	0.56 W

Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Technical data

General

Maximum load current	17.5 A
Nominal current I_N	17.5 A
Nominal voltage U_N	500 V
Open side panel	Yes
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Static insulating material application in cold	-60 °C
Behavior in fire for rail vehicles (DIN 5510-2)	Test passed
Flame test method (DIN EN 60695-11-10)	V0
Oxygen index (DIN EN ISO 4589-2)	>32 %
NF F16-101, NF F10-102 Class I	2
NF F16-101, NF F10-102 Class F	2
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

Dimensions

Width	3.5 mm
End cover width	2.2 mm
Length	33.55 mm
Height NS 15	28.1 mm

Connection data

Connection method	Push-in connection
Connection in acc. with standard	IEC 60947-7-1
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section AWG min.	26
Conductor cross section AWG max.	14
Conductor cross section flexible min.	0.14 mm ²
Conductor cross section flexible max.	1.5 mm ²
Min. AWG conductor cross section, flexible	26
Max. AWG conductor cross section, flexible	14
Conductor cross section flexible, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	1.5 mm ²

Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Technical data

Connection data

Conductor cross section flexible, with ferrule with plastic sleeve min.	0.14 mm²
Conductor cross section flexible, with ferrule with plastic sleeve max.	1 mm²
Stripping length	8 mm ... 10 mm
Internal cylindrical gage	A1 / B1

Standards and Regulations

Connection in acc. with standard	CSA
Connection in acc. with standard	IEC 60947-7-1
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
China RoHS	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27141121
eCl@ss 4.1	27141121
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120
eCl@ss 9.0	27141120

ETIM

ETIM 3.0	EC001329
ETIM 4.0	EC000902
ETIM 5.0	EC000897
ETIM 6.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

IECEx / ATEX / CSA / UL Recognized / cUL Recognized / BV / GL / DNV / VDE Zeichengenehmigung / EAC / EAC / cULus Recognized /

Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Approvals

Approval details

IECEX	
Nominal voltage UN	352 V
Nominal current IN	14.5 A
mm²/AWG/kcmil	0.14-1.5

ATEX	
Nominal voltage UN	352 V
Nominal current IN	14.5 A
mm²/AWG/kcmil	0.14-1.5

CSA			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	15 A	15 A	5 A
mm²/AWG/kcmil	26-14	26-14	26-14

UL Recognized			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	15 A	15 A	5 A
mm²/AWG/kcmil	26-14	26-14	26-14

cUL Recognized			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	15 A	15 A	5 A
mm²/AWG/kcmil	26-14	26-14	26-14

BV

GL

DNV

VDE Zeichengenehmigung

Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Approvals

Nominal voltage UN	500 V
Nominal current IN	17.5 A
mm²/AWG/kcmil	0.14-1.5

EAC EAC

EAC

cULus Recognized 

Accessories

End cover

D-MPT 1,5/S - 3248120



Screwdriver tools

SZF 0-0,4X2,5 - 1204504



ST-BW 0 - 1200135



Partition plate

Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Accessories

ATP-MBK - 1413227



Jumper

FBS 2-3,5 - 3213014



FBS 3-3,5 - 3213027



FBS 4-3,5 - 3213030



FBS 5-3,5 - 3213043



Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Accessories

FBS 10-3,5 - 3213056



FBS 20-3,5 - 3213069



FBS 2-3,5 BU - 3213086



FBS 3-3,5 BU - 3213099



FBS 4-3,5 BU - 3213109



FBS 5-3,5 BU - 3213112



Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Accessories

FBS 10-3,5 BU - 3213125



FBS 20-3,5 BU - 3213138



FBS 2-3,5 GY - 3213153



FBS 3-3,5 GY - 3213167



FBS 4-3,5 GY - 3213180



Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Accessories

FBS 5-3,5 GY - 3213183



FBS 10-3,5 GY - 3213196



FBS 20-3,5 GY - 3213206



DIN rail

NS 15 UNPERF 2000MM - 1401695



NS 15 PERF 2000MM - 1401682

Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Accessories

NS 15 AL PERF 2000MM - 1401763



NS 15 WH PERF 2000MM - 1204096



End block

CLIPFIX 15 - 3022263



Terminal marking

ZBF 3,5:UNBEDRUCKT - 0829392



UCT-TMF 3,5 - 0829486



Labeled terminal marker

Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Accessories

ZBF 3,5 CUS - 0829394



ZBF 3,5,LGS:FORTL.ZAHLEN - 0801406



ZBF 3,5,QR:FORTL.ZAHLEN - 0801407



UCT-TMF 3,5 CUS - 0829644



Test plug terminal block

MPS-MT - 0201744



Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Accessories

PS-3,5 - 3031010



PS-3,5/E - 3031012



Insulating sleeve

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Accessories

MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



Planning and marking software

CLIP-PROJECT ADVANCED - 5146040



Mini feed-through terminal block - MPT 1,5/S BU - 3248101

Accessories

CLIP-PROJECT PROFESSIONAL - 5146053



Partition plate

DP PS-3,5 - 3031011



Drawings

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>