


Features

- * High efficiency
- * Popular G-3 1/2 diameter package

Package Dimensions



Lens	Source Color
Diffuse	Warm White

Notes:

1. All dimensions are in millimeters.
2. Tolerance is $\pm 0.25\text{mm}$ unless otherwise noted.
3. Lead spacing is measured where the leads emerge from the package.
4. Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commission International De L'Eclairage) eye-response curve.
5. $\theta_{1/2}$ is the off-axis angle at which the luminous intensity is half the axial luminous intensity.
6. The dominant wavelength, λ_d is derived from the CIE chromaticity diagram and represents the single Wavelength which defines the color of the device.

Absolute Maximum Ratings at Ta=25°C

Symbol	Parameter	Maximum Rating	Unit
Pd	Power Dissipation	170	mW
IFP	Peak Forward Current (1/10 Duty Cycle, 0.1ms Pulse Width)	100	mA
IF	DC Forward Current	15	mA
VR	Reverse Voltage	5	V
ESD	Electrostatic Discharge	2000	V
TOPR	Operating Temperature	-40°C to +80°C	°C
TSTG	Storage Temperature	-40°C to +85°C	°C
TSOL	Soldering Temperature	260°C for 5 Seconds	°C

Electrical / Optical Characteristics at TA=25°C

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test Condition
Luminous Intensity	I _v	1200		2800	mcd	IF=15mA
Viewing Angle	2θ _{1/2}		35		deg	IF=15mA
Peak Emission Wavelength	λ _p		-----		nm	IF=15mA
Chromaticity Coordinates	X	0.47		0.52		IF=15mA
	y	0.37		0.42		
Forward Voltage	V _F			4.5	V	IF=15mA
Reverse Current	I _R			10	uA	VR=5V

Typical Electrical / Optical Characteristics Curves

(25°C Ambient Temperature Unless Otherwise Noted)




Fig.1 Relative Spectrum of Emission




Fig.2 Forward Current vs. Forward Voltage






Fig.3 Forward Current Derating Curve



Ambient Temperature Ta (°C)

Fig.4 Luminous Intensity

Vs. Ambient Temperature



Forward Current (mA)

Fig.5 Relative Luminous Intensity

Vs. Forward Current




Fig.6 Spatial Distribution