

Energizer® Universal Headlight

HD33A4


The *Energizer*® Universal Headlight is a convenient solution for a variety of tasks, especially the ones that require hands-free operation. Using efficient LED technology, the *Energizer* Universal Headlight provides consumers with bright, powerful light that lasts hour after hour. The pivoting head offers flexibility when choosing where to direct the light beam, while a handy slide switch allows users to easily activate the light. The red LED mode enables users to preserve night vision, while the base mode provides bright, white light that is excellent for a variety of tasks. The *Energizer* Universal Headlight features a durable construction and an adjustable head strap that makes it easy to use. Powerful and versatile, the Universal Headlight is a helpful solution for any household, work or outdoor activity.



Provides 60 Lumens of Light



Provides Run Time of 19 Hours



Shines Light on Objects up to 20 Meters Away



Sustains 1 Meter Drop Test.

DESIGN BENEFITS

- ✓ Red LED to preserve night vision
- ✓ Pivoting head to orient light wherever needed
- ✓ Easy to operate slide switch
- ✓ Reliable construction with shatterproof lens

LIGHT AND POWER SOURCE

- ✓ Features LED Technology
- ✓ Operates on 3 AAA Batteries

CERTIFICATES AND COMPLIANCE

CE RoHS

EMC, EN62471, FCC



Tested according to ANSI/NEMA FL1 Standards. Results based on: Energizer® MAX, Alkaline / E92

PERFORMANCE BENEFITS

- ✓ Up to 5X brighter than Standard LED Technology
- ✓ Long Run Time

SPECIFICATIONS

Weight Excluding Batteries:

40 Grams / 1.4 Ounces

Dimensions:

45mm x 67mm x 40mm / 1.8" x 2.6" x 1.6"

NUMBER OF OPERATING MODES: 2

Mode	Lumens (lm)	Runtime (h)	Beam Distance (m)
White	60	19	20
Red			

Before using your flashlight, please read all instructions and cautionary marking on the package and the light.

This datasheet contains information specific to products manufactured at the time publication. Contents do not constitute a claim or warranty.

©2015 Energizer