


KERN KFP 30V20SM

KERN

Platform: weighing plate of stainless steel, painted steel base, silicone-coated aluminium load cell with protection against dust and water splashes IP65



Category

Brand	KERN
Product category	Component
Product group	Platform
Product family	KFP-V20-IP65

Measuring System

Weighing capacity [Max]	15 kg; 30 kg
Readability [d]	1 g
Minimum weight [Min]	100 g; 200 g
Load cell connection	4-wire
Load cell OIML class	C3
Loadcell type	aluminium IP65 silicone-coated

Construction

Dimensions weighing surface (W×D)	300×240 mm
Dimensions weighing surface	300×240 mm
Dimensions weighing platform (W×D×H)	300×240×109 mm
Material weighing plate	stainless steel
Material platform	steel, powder-coated
Material load cell(s)	aluminium
Levelling feet adjustable	✓
Transport safety lock - bolt torque	0,1 Nm
Cable length	2,5 m
Allowed cable length display device [Max]	3 m
Platform Construction	Single-Cell
Load cells - number	1

Functions

IP protection - load cell	IP65
---------------------------	------

Environmental conditions

Ambient temperature [Max]	40 °C
---------------------------	-------

Approval

Conformity assessment possible ex works	✓
Verification scale interval [e]	5 g; 10 g

Services (optional)

Article number for conformity assessment	965-228
Article number for DAkkS calibration	963-128

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	693×414×225 mm
Shipping method	Parcel service
Net weight approx.	3,8 kg
Gross weight approx.	6 kg
Shipping weight	12,9 kg

Product information

GTIN/EAN number	4045761250154
REACH classification	no prohibited substances

Pictograms

STANDARD



FACTORY

