

The cooled camera for professional fluorescence examinations



Features

- The ODC 861 camera with Peltier cooling technology has been specially designed for fluorescent applications. It is able to significantly compensate for image noise associated with weak lighting. Due to its high resolution and light-sensitive Sony CMOS colour sensor it proves first-class images. The practical, sturdy storage box serves as protection and for transportation of this premium camera
- Realtime images can be transferred straight to a PC or laptop using the integrated USB 3.0 interface. As an alternative, 2 USB 2.0 interfaces are available, to operate the camera with the software KERN Microscope VIS
- Power supply is from an external 12 V power unit
- Please order the appropriate C-mount adapter (only 1,0x possible) to fit your KERN microscope now
- Black balance possible

Note: Can only be used in combination with compound microscopes

STANDARD



Model	Resolution	Interface	FPS	Sensor	Sensor size	Colour/ Monochrome	Supported operating system
KERN							
ODC 861	20 MP	USB 3.0	5 – 30	CMOS	1"	colour	Win XP, Vista, 7, 8, 10, 11

Eyepiece Cameras – USB 2.0/3.0 KERN ODC-87 · ODC-88



ODC-87, ODC-88



Eyepiece camera fixed into the tube

Features

- With the KERN eyepiece cameras you can convert your standard microscope to a digital microscope, by replacing one eyepiece of your non-digital microscope with an eyepiece camera and connect this to your computer via USB
- The universal eyepiece can be connected to the microscope as well as to a laptop or PC using the USB cable (2.0 or 3.0, see table)
- The power supply is through the USB cable, which means that no additional power supply is required
- Your daily work is made significantly easier with the very best synchronisation, a high frame rate as well as stable image performance together with our software
- As well as the camera, the delivery includes a USB cable (length: 1,5 m), two eyepiece adapters and an object micrometer to calibrate the software
- Possible tube diameters:
 - 23,2 mm (Standard)
 - 30,0 mm (Eyepiece adapter)
 - 30,5 mm (Eyepiece adapter)
- "Microsoft VIS" PC software for convenient image processing and analysis - available on our website
www.kern-sohn.com/shop/en/DOWNLOADS

STANDARD



Model	Resolution	Interface	FPS	Sensor	Sensor size	Colour/ Monochrome	Supported operating system
KERN							
ODC 874	3 MP	USB 2.0	3 – 7,5	CMOS	1/2,7"	colour	Win XP, Vista, 7, 8, 10, 11
ODC 881	5 MP	USB 3.0	15 – 30	CMOS	1/2,5"	colour	Win XP, Vista, 7, 8, 10, 11