

KERN PLJ 2000-3A



Range of precision balances with enormous weighing capacities – ideal for heavy tare containers or large samples



Category

Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PLJ

Measuring System

Automatic adjustment - Standard temperature deviation	1,2 °C
Weighing system	Force compensation
Weighing capacity [Max]	2100 g
Readability [d]	0,001 g
Reproducibility	0,002 g
Linearity	± 0,004 g
Resolution	2.100.000
Tare range	2100 g
Adjustment options	Internal calibration (automatic)
Recommended adjusting weight	2 kg (E2)
Stabilization time	2 s
Warm-up time	8 h
Eccentric loading at 1/3 [Max]	0,005 g
USP Minimum weight of sample (k = 2, U = 0.1%)	4 g
Construction type of the scale	Single-range balance

Units

g
mg
gn
dwt
tl (Tw)
tl (HK)
ozt
tl (Singap, Malays)
ct

mo
lb
oz

Weighing capacity [Max] (ct)	10500 ct
Maximum creep (15 minutes)	10 mg
Maximum creep (30 minutes)	20 mg
Default unit	g

Display

Display type	LCD graphic
Display backlight	✓
Display screen size	132×38 mm
Display digit height - smallest digit	4 mm
Display digit height	15 mm
Languages of the user interface	English

Construction

Dimension housing (W×D×H)	210×340×330 mm
Dimensions completely mounted (W×D×H)	210×340×330 mm
Dimensions rectangular draught shield - inner (W×D×H)	160×170×225 mm
Dimensions rectangular draught shield - outer (W×D×H)	172×185×245 mm
Dimensions weighing surface (Ø)	110 mm
Dimensions weighing surface	110 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	stainless steel
Material draught shield	glass
Level indicator	✓
Levelling feet adjustable	✓
Transport safety lock - bolt torque	0,1 Nm

Functions

PreTare function	✓
Recipe/summing level	Rez B (Net-total, memory with plain text designations + setpoint, also for printout)
Recipe weighing - number of database entries	99
Recipe weighing - number of ingredients per database entry	20
Percentage determination	✓
Density determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual

KERN PLJ 2000-3A



Range of precision balances with enormous weighing capacities – ideal for heavy tare containers or large samples

Underfloor weighing	Eye (included in delivery)
Function for averaging under unstable weighing conditions	✓
Time display	✓
Capacity - Display	✓
Standby function	✓
Counting function	✓
Counting resolution (laboratory conditions)	42.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	50 mg
Smallest piece weight when piece counting - normal conditions	500 mg
Reference quantity	10, 25, 50, 100, n (any number of pieces)
	off
Auto-off interval(s) in mains power mode	5 min 2 min 15 min
Tare function	manual (multi)
Number of keys for operation	6

Interface

Interfaces	RS-232 standard
------------	-----------------

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	24 V 1 A
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 10,5 mm

Environmental conditions

Ambient temperature [Min]	15 °C
---------------------------	-------

Ambient temperature [Max]	35 °C
---------------------------	-------

Humidity of environment [Max]	80 %
-------------------------------	------

Storage temperature [Max]	40 °C
---------------------------	-------

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration	963-103
--------------------------------------	---------

Article number for certificate of conformity	969-517
--	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	515×400×615 mm
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	8 kg
Shipping weight	25,3 kg

Product information

GTIN/EAN number	4045761243224
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

