



Discover more details and matching accessories online!

Platform scale with IP65 dust and spray protection, verification optional

- Features**

 - Platform scale protected to IP65 with stainless steel display device, for industrial applications, hygienic and easy to clean
 - 1** Platform: weighing plate of stainless steel, painted steel base, silicone-coated aluminium load cell with protection against dust and water splashes IP65
 - Display device: stainless steel, protection against dust and water splashes IP65, flexible positioning, for details see KERN KFE-TM
 - Weighing with tolerance range: a visual and audible signal helps with portioning, dispensing or grading
 - Hold function: When the weighing conditions are unstable, a stable weight is calculated determining an average value
- Technical data**

 - Large backlit LCD display, digit height 22 mm
 - Weighing platform dimensions, stainless steel
 - A** W×D×H 300×240×109 mm, see larger picture
 - B** W×D×H 400×300×117 mm
 - C** W×D×H 500×400×127 mm
 - D** W×D×H 650×500×139 mm
 - Dimensions of display device W×D×H 195×120×70 mm
 - Rechargeable battery pack integrated, as standard, operating time up to 35 h without backlight, charging time approx. 12 h
 - Cable length of display device approx. 3 m
 - Permissible ambient temperature -10 °C/40 °C

STANDARD

OPTION

FACTORY

Model	Weighing capacity [Max] kg	Readability [d] g	Verification value [e] g	Minimal load [Min] g	Net weight approx. kg	Weighing plate	Options	
							Verification	Calibr. Certificate
KERN								DAkKS accr. KERN
SFE 6K-3NM	6	2	2	40	6	A	965-228	963-128
SFE 10K-3NM	15	5	5	100	6	A	965-228	963-128
SFE 10K-3LNM	15	5	5	100	8	B	965-228	963-128
SFE 30K-2NM	30	10	10	200	6	A	965-228	963-128
SFE 60K-2NM	60	20	20	400	8	B	965-229	963-129
SFE 60K-2LNM	60	20	20	400	12	C	965-229	963-129
SFE 100K-2NM	150	50	50	1000	8	B	965-229	963-129
SFE 100K-2LNM	150	50	50	1000	12	C	965-229	963-129
SFE 100K-2XLNM	150	50	50	1000	22	D	965-229	963-129
SFE 300K-1LNM	300	100	100	2000	22	D	965-229	963-129

Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order. The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.