

## Interface module - VIP-2/PT/D 9SUB/M - 2903777

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with push-in connections and male D-SUB miniature pin strip, for mounting on NS 35 rails, 9-pos.

The illustration shows a 15 position version with male D-sub connector.



### Key commercial data

package_quantity	1
GTIN	4046356796521

### Technical data

#### Dimensions

Width	36.8 mm
Height	72.1 mm
Depth	46.6 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### General

Max. perm. operating voltage	25 V AC
Max. perm. operating voltage	60 V DC
Max. perm. current (per branch)	2 A
Number of positions	9
Status display	No
Mounting position	any

#### Connection data for connection 1

Connection name	Field level
Connection method	Push-in connection
Stripping length	8 mm
Conductor cross section solid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section flexible	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>

# Interface module - VIP-2/PT/D 9SUB/M - 2903777

## Technical data

### Connection data for connection 1

<b>Conductor cross section AWG</b>	26 ... 14
------------------------------------	-----------

### Connection data for connection 2

<b>Connection name</b>	Controller level
<b>Connection method</b>	D-SUB pin strip
<b>Number of connections</b>	1
<b>Number of positions</b>	9

### Standards and Regulations

<b>Connection in acc. with standard</b>	CSA
<b>Standards/regulations</b>	IEC 60664
<b>Standards/regulations</b>	DIN EN 50178
<b>Rated surge voltage</b>	1.2 kV
<b>Degree of pollution</b>	2
<b>Overvoltage category</b>	II

## Classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27250313
<b>eCl@ss 4.1</b>	27250313
<b>eCl@ss 5.0</b>	27250313
<b>eCl@ss 5.1</b>	27250313
<b>eCl@ss 7.0</b>	27141152
<b>eCl@ss 8.0</b>	27141152
<b>eCl@ss 9.0</b>	27141152

### ETIM

<b>ETIM 4.0</b>	EC002780
<b>ETIM 5.0</b>	EC002780
<b>ETIM 6.0</b>	EC002780

### UNSPSC

<b>UNSPSC 6.01</b>	30211916
<b>UNSPSC 7.0901</b>	39121515
<b>UNSPSC 11</b>	39121515
<b>UNSPSC 12.01</b>	39121542
<b>UNSPSC 13.2</b>	39121515

## Approvals

---

CSA / UL Recognized / cUL Recognized / EAC / EAC / cULus Recognized /

---

# Interface module - VIP-2/PT/D 9SUB/M - 2903777

## Approvals

### Approval details

CSA ®	
Nominal voltage UN	105 V
Nominal current IN	2 A
mm <sup>2</sup> /AWG/kcmil	26-14

UL Recognized	
Nominal voltage UN	125 V
Nominal current IN	2 A
mm <sup>2</sup> /AWG/kcmil	26-14

cUL Recognized	
Nominal voltage UN	125 V
Nominal current IN	2 A
mm <sup>2</sup> /AWG/kcmil	26-14

EAC EAC	
---------	--

EAC	
-----	--

cULus Recognized	
------------------	--

## Accessories

### System cable

CABLE-D 9SUB/B/S/ 50/KONFEK/S - 2299987



CABLE-D 9SUB/B/S/100/KONFEK/S - 2299990



## Interface module - VIP-2/PT/D 9SUB/M - 2903777

### Accessories

---

CABLE-D 9SUB/B/S/150/KONFEK/S - 2300009



CABLE-D 9SUB/B/S/200/KONFEK/S - 2302010



CABLE-D 9SUB/B/S/300/KONFEK/S - 2302023



CABLE-D 9SUB/B/S/400/KONFEK/S - 2302036



CABLE-D 9SUB/B/S/600/KONFEK/S - 2302049



## Interface module - VIP-2/PT/D 9SUB/M - 2903777

### Accessories

CABLE D-SUB-S/.../.../... - 2302340



CABLE-D 9SUB/B/B/100/KONFEK/S - 2305415



CABLE-D 9SUB/B/B/200/KONFEK/S - 2305428



CABLE-D 9SUB/B/B/300/KONFEK/S - 2305431



CABLE D-SUB-B-B-S/.../.../... - 2302421



### Terminal marking

## Interface module - VIP-2/PT/D 9SUB/M - 2903777

### Accessories

UC-TM 4 - 0818111



UC-TM 6 - 0818085



ZB 5,08:UNBEDRUCKT - 0809793



ZB 22:UNBEDRUCKT - 0811862



### Printing system


BLUEMARK X1 - 5147777



### Drawings

## Interface module - VIP-2/PT/D 9SUB/M - 2903777

Circuit diagram



Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>