




Discover more details and matching accessories online!

High-resolution floor scale with 2×3000 [d] and the best price-to performance ratio

Features

- Weighing bridge out of anti-slip corrugated steel, 4 load cells, alloy steel, silicone-coated, IP67
- Welded platform with screw holes to lift the scale for easy cleaning
- Easy levelling of the weighing bridge as well as access to the junction box from above
- Simple and convenient 4-key operation
- Wall mount for display device, standard
- 1 Our floor scales are delivered in a robust wooden box. This protects the high-quality weighing technology from environmental influences and stresses during transportation

Technical data

- Large LCD display, digit height 25 mm
- Weighing platform dimensions, steel, powder-coated
  - A W×D×H 1000×1000×108 mm
  - B W×D×H 1200×1500×108 mm
  - C W×D×H 1500×1500×108 mm
- Dimensions of display device W×D×H 235×114×51 mm
- Optional battery operation, 4×1.5 V AA not included in scope of delivery, operating time up to 60 h
- Cable length of display device approx. 5 m
- Permissible ambient temperature -10 °C/40 °C

Shipment via freight forwarder. Please ask for dimensions, gross weight, shipping costs

STANDARD



OPTION



Model KERN	Weighing capacity [Max] kg	Readability [d] kg	Weighing plate	Net weight approx. kg	Options Calibr. Certificate DAkkS accr. KERN
BIC 600K-1S	300 | 600	0,1 | 0,2	A	70	963-130
BIC 600K-1	300 | 600	0,1 | 0,2	B	150	963-130
BIC 1T-4S	600 | 1500	0,2 | 0,5	A	70	963-130
BIC 1T-4	600 | 1500	0,2 | 0,5	B	150	963-130
BIC 3T-3	1500 | 3000	0,5 | 1	B	150	963-132
BIC 3T-3L	1500 | 3000	0,5 | 1	C	155	963-132

Multi-range balance, with increasing load it switches automatically to the next largest weighing range [Max] and readout [d] and when the load is fully removed, the balance switches back to the lower range