

Potential distributors - VIP-3/PT/PDM-2/16 - 2903797

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with two equipotential busbars (P1, P2) for potential distribution, for mounting on NS 35 rails. Module width: 41.9 mm



Key commercial data

package_quantity	1
GTIN	4046356796712

Technical data

Dimensions

Width	41.9 mm
Height	75.8 mm
Depth	63 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	250 V AC/DC
Max. current carrying capacity per branch	15 A
Total current	30 A (per potential)
Potential connections	Per potential (P1, P2) 2 power/8 distributor terminal blocks
Mounting position	any
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Degree of pollution	2
Overvoltage category	III

Connection data, supply

Connection method	Push-in-/Spring-cage connection
Stripping length	15 mm
Conductor cross section solid	0.25 mm ² ... 6 mm ²
Conductor cross section flexible	0.25 mm ² ... 4 mm ²

Potential distributors - VIP-3/PT/PDM-2/16 - 2903797

Technical data

Connection data, supply

Conductor cross section AWG	24 ... 10
Number of connections	2

Connection data, distribution

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross section solid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross section AWG	26 ... 14
Number of connections	16

Standards and Regulations

Connection in acc. with standard	CSA
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Degree of pollution	2
Overvoltage category	III

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27400609
eCl@ss 7.0	27400609
eCl@ss 8.0	27400609
eCl@ss 9.0	27400609

ETIM

ETIM 4.0	EC001894
ETIM 5.0	EC001894
ETIM 6.0	EC001894

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121432

Potential distributors - VIP-3/PT/PDM-2/16 - 2903797

Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized /

Approval details

CSA	
Nominal voltage UN	250 V
Nominal current IN	15 A
mm ² /AWG/kcmil	26-14

UL Recognized	
Nominal voltage UN	250 V
Nominal current IN	15 A
mm ² /AWG/kcmil	26-14


cUL Recognized	
Nominal voltage UN	250 V
Nominal current IN	15 A
mm ² /AWG/kcmil	26-14

EAC	
-----	--

cULus Recognized	
------------------	--


Drawings

Dimensional drawing



Potential distributors - VIP-3/PT/PDM-2/16 - 2903797

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>