

Interface module - VIP-2/PT/D15SUB/M - 2903779

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with push-in connections and male D-SUB miniature pin strip, for mounting on NS 35 rails, 15-pos.

Key commercial data

package_quantity	1
GTIN	4046356796545

Technical data

Dimensions

Width	46.9 mm
Height	72.1 mm
Depth	63 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. perm. operating voltage	25 V AC
Max. perm. operating voltage	60 V DC
Max. perm. current (per branch)	2 A
Number of positions	15
Status display	No
Mounting position	any

Connection data for connection 1

Connection name	Field level
Connection method	Push-in connection
Stripping length	8 mm
Conductor cross section solid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross section AWG	26 ... 14

Connection data for connection 2

Connection name	Controller level
Connection method	D-SUB pin strip

Interface module - VIP-2/PT/D15SUB/M - 2903779

Technical data

Connection data for connection 2

Number of connections	1
Number of positions	15

Standards and Regulations

Connection in acc. with standard	CSA
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Rated surge voltage	1.2 kV
Degree of pollution	2
Overvoltage category	II

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152
eCl@ss 9.0	27141152

ETIM

ETIM 4.0	EC002780
ETIM 5.0	EC002780
ETIM 6.0	EC002780

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121515
UNSPSC 11	39121515
UNSPSC 12.01	39121542
UNSPSC 13.2	39121432

Approvals

CSA / UL Recognized / cUL Recognized / EAC / EAC / EAC / cULus Recognized /

Approval details

CSA ®	
Nominal voltage UN	105 V

Interface module - VIP-2/PT/D15SUB/M - 2903779

Approvals

Nominal current I _N	2 A
mm ² /AWG/kcmil	26-14

UL Recognized 	
Nominal voltage U _N	125 V
Nominal current I _N	2 A
mm ² /AWG/kcmil	26-14

cUL Recognized 	
Nominal voltage U _N	125 V
Nominal current I _N	2 A
mm ² /AWG/kcmil	26-14

EAC 
--





cULus Recognized 

Accessories

System cable

CABLE-D15SUB/B/S/ 50/KONFEK/S - 2302052



CABLE-D15SUB/B/S/100/KONFEK/S - 2302065



Interface module - VIP-2/PT/D15SUB/M - 2903779

Accessories

CABLE-D15SUB/B/S/150/KONFEK/S - 2302078



CABLE-D15SUB/B/S/200/KONFEK/S - 2302081



CABLE-D15SUB/B/S/300/KONFEK/S - 2302094



CABLE-D15SUB/B/S/400/KONFEK/S - 2302104



CABLE-D15SUB/B/S/600/KONFEK/S - 2302117



CABLE D-SUB-S/.../.../... - 2302340



Interface module - VIP-2/PT/D15SUB/M - 2903779

Accessories

CABLE-D15SUB/B/B/100/KONFEK/S - 2305444



CABLE-D15SUB/B/B/200/KONFEK/S - 2305457



CABLE-D15SUB/B/B/300/KONFEK/S - 2305460



CABLE D-SUB-B-B-S/.../.../... - 2302421



Terminal marking

UC-TM 4 - 0818111



Interface module - VIP-2/PT/D15SUB/M - 2903779

Accessories

UC-TM 6 - 0818085



ZB 5,08:UNBEDRUCKT - 0809793



ZB 22:UNBEDRUCKT - 0811862




Printing system

BLUEMARK X1 - 5147777



Drawings

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>