

Interface module - VIP-3/PT/D37SUB/M - 2903783

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with push-in connections and male D-SUB miniature pin strip, for mounting on NS 35 rails, 37-pos.

Key commercial data

package_quantity	1
GTIN	4046356796583

Technical data

Dimensions

Width	72.3 mm
Height	75.8 mm
Depth	63 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. perm. operating voltage	25 V AC
Max. perm. operating voltage	60 V DC
Max. perm. current (per branch)	2 A
Number of positions	37
Status display	No
Mounting position	any

Connection data for connection 1

Connection name	Field level
Connection method	Push-in connection
Stripping length	8 mm
Conductor cross section solid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross section AWG	26 ... 14

Connection data for connection 2

Connection name	Controller level
Connection method	D-SUB pin strip

Interface module - VIP-3/PT/D37SUB/M - 2903783

Technical data

Connection data for connection 2

Number of connections	1
Number of positions	37

Standards and Regulations

Connection in acc. with standard	CSA
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Rated surge voltage	1.2 kV
Degree of pollution	2
Overvoltage category	II

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152
eCl@ss 9.0	27141152

ETIM

ETIM 4.0	EC002780
ETIM 5.0	EC002780
ETIM 6.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121432

Approvals

CSA / UL Recognized / cUL Recognized / EAC / EAC / cULus Recognized /

Approval details

CSA ®	
Nominal voltage UN	105 V

Interface module - VIP-3/PT/D37SUB/M - 2903783

Approvals

Nominal current I _N	2 A
mm ² /AWG/kcmil	26-14

UL Recognized 	
Nominal voltage U _N	125 V
Nominal current I _N	2 A
mm ² /AWG/kcmil	26-14

cUL Recognized 	
Nominal voltage U _N	125 V
Nominal current I _N	2 A
mm ² /AWG/kcmil	26-14

EAC 
--

ERC

cULus Recognized 

Accessories

System cable

CABLE-D37SUB/B/S/ 50/KONFEK/S - 2302191



CABLE-D37SUB/B/S/100/KONFEK/S - 2302201



Interface module - VIP-3/PT/D37SUB/M - 2903783

Accessories

CABLE-D37SUB/B/S/150/KONFEK/S - 2302214



CABLE-D37SUB/B/S/200/KONFEK/S - 2302227



CABLE-D37SUB/B/S/300/KONFEK/S - 2302230



CABLE-D37SUB/B/S/400/KONFEK/S - 2302243



CABLE-D37SUB/B/S/600/KONFEK/S - 2302256



CABLE D-SUB-S/.../.../... - 2302340



Interface module - VIP-3/PT/D37SUB/M - 2903783

Accessories

CABLE-D37SUB/B/B/ 100/KONFEK/S - 2305509



CABLE-D37SUB/B/B/ 200/KONFEK/S - 2305512



CABLE-D37SUB/B/B/ 300/KONFEK/S - 2305525



CABLE D-SUB-B-B-S/.../.../... - 2302421



CABLE D-SUB-B-B-S/.../.../... - 2302421



Terminal marking

Interface module - VIP-3/PT/D37SUB/M - 2903783

Accessories

UC-TM 4 - 0818111



UC-TM 6 - 0818085



ZB 5,08:UNBEDRUCKT - 0809793



ZB 22:UNBEDRUCKT - 0811862



Printing system


BLUEMARK X1 - 5147777



Drawings

Interface module - VIP-3/PT/D37SUB/M - 2903783

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>