

Interface module - VIP-3/PT/FLK40 - 2903793

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with push-in connection and flat-ribbon cable connector, for mounting on NS 35 DIN rails, with pin strip plus short and long locking latches for socket strips, 40-pos.

Key commercial data

package_quantity	1
GTIN	4046356796675

Technical data

Dimensions

Width	77.4 mm
Height	75.8 mm
Depth	63 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. perm. operating voltage	60 V AC/DC
Max. perm. current (per branch)	1 A
Number of positions	40
Status display	No
Mounting position	any

Connection data for connection 1

Connection name	Field level
Connection method	Push-in connection
Stripping length	8 mm
Conductor cross section solid	0.14 mm² ... 2.5 mm²
Conductor cross section flexible	0.14 mm² ... 2.5 mm²
Conductor cross section AWG	26 ... 14

Connection data for connection 2

Connection name	Controller level
Connection method	IDC/FLK pin strip
Number of connections	1

Interface module - VIP-3/PT/FLK40 - 2903793

Technical data

Connection data for connection 2

Number of positions	40
Pitch	2.54 mm

Supported controller

Controller	ALLEN-BRADLEY SLC 500
- suitable I/O card	1746 OB 32
- suitable I/O card	1746 OV 32
- suitable I/O card	1746 IB 32
- suitable I/O card	1746 IV 32

Standards and Regulations

Connection in acc. with standard	CSA
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Rated surge voltage	0.6 kV
Degree of pollution	2
Overvoltage category	II

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152
eCl@ss 9.0	27141152

ETIM

ETIM 4.0	EC002780
ETIM 5.0	EC002780
ETIM 6.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121432

Approvals

Interface module - VIP-3/PT/FLK40 - 2903793

Approvals

Approval details

CSA ®	
Nominal voltage UN	125 V
Nominal current IN	1 A
mm²/AWG/kcmil	26-14

UL Recognized ⚡	
Nominal voltage UN	125 V
Nominal current IN	1 A
mm²/AWG/kcmil	26-14

cUL Recognized ⚡	
Nominal voltage UN	125 V
Nominal current IN	1 A
mm²/AWG/kcmil	26-14

EAC EAC

EAC

cULus Recognized ⚡

Accessories

System cable

VIP-CAB-FLK40/0,14/0,5M - 2318787



Interface module - VIP-3/PT/FLK40 - 2903793

Accessories

VIP-CAB-FLK40/0,14/1,0M - 2318790



VIP-CAB-FLK40/0,14/1,5M - 2318800



VIP-CAB-FLK40/0,14/2,0M - 2318813



VIP-CAB-FLK40/0,14/3,0M - 2318826



VIP-CAB-FLK40/0,14/4,0M - 2318839



VIP-CAB-FLK40/0,14/6,0M - 2318842



Interface module - VIP-3/PT/FLK40 - 2903793

Accessories

VIP-CAB-FLK40-0,14/... - 2318855



FLK 40/EZ-DR/ 50/KONFEK - 2288985



FLK 40/EZ-DR/ 100/KONFEK - 2288998



FLK 40/EZ-DR/ 150/KONFEK - 2289007



FLK 40/EZ-DR/ 200/KONFEK - 2289010



Interface module - VIP-3/PT/FLK40 - 2903793

Accessories

FLK 40/EZ-DR/ 250/KONFEK - 2289023



FLK 40/EZ-DR/ 300/KONFEK - 2289036



FLK 40/EZ-DR/ 350/KONFEK - 2289049



FLK 40/EZ-DR/ 400/KONFEK - 2289052



FLK 40/EZ-DR/ 600/KONFEK - 2299589



FLK 40/EZ-DR/ 800/KONFEK - 2299592



Interface module - VIP-3/PT/FLK40 - 2903793

Accessories

FLK 40/EZ-DR/1000/KONFEK - 2299602



FLK EZ-DR-S.../.../... - 2295046



Terminal marking

UC-TM 4 - 0818111



UC-TM 6 - 0818085



ZB 5,08:UNBEDRUCKT - 0809793



Interface module - VIP-3/PT/FLK40 - 2903793

Accessories

ZB 22:UNBEDRUCKT - 0811862




Printing system

BLUEMARK X1 - 5147777



Drawings

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>