



Discover more details and matching accessories online!

Industrial counting scale with convenient decimal keypad and high counting resolution, verification optional

Features

- Display device with large keypad and high-contrast LCD display for easy entry and reading of, e.g., tare weights, reference weights, limit values etc.
- Three displays for weight display (verifiable), reference weight, total pieces
- 100 item memories for master data such as reference weight, reference quantity, container weight (PRE-TARE) etc.

- The manual reference weight optimisation gradually improves the average value of the piece weight
- Totalising of pieces when counting
- Printout with date and time
- Protective working cover over the display device included with the delivery

Technical data

- Large backlit LCD displays, digit height 16,5 mm
- Weighing platform dimensions W×D×H, stainless steel
 - A** 230×230×110 mm
 - B** 300×240×110 mm
 - C** 400×300×120 mm
 - D** 500×400×120 mm
 - E** 650×500×140 mm
- Dimensions of display device W×D×H 260×150×65 mm
- Cable length of display device approx. 3 m
- Permissible ambient temperature -10 °C/40 °C

STANDARD



OPTION



FACTORY



IFS-M

Model	Weighing capacity [Max] kg	Readability [d] g	Verification value [e] g	Minimal load [Min] g	Smallest part weight (Normal) g/piece	Net weight approx. kg	Weighing plate	Options		
								Verification	Calibr.	Certificate
KERN								M KERN	DAkKS accr. KERN	
Multi-range balance, with increasing load it switches automatically to the next largest weighing range [Max] and readout [d] and when the load is fully removed, the balance switches back to the lower range										
IFS 6K-4S*	3 6	0,1 0,2	-	-	1	3,8	A	-		963-128
IFS 10K-4	6 15	0,1 0,2	-	-	2	6	B	-		963-128
IFS 30K0.2DL	12 30	0,2 0,5	-	-	5	7	C	-		963-128
IFS 60K0.5D	30 60	0,5 1	-	-	10	7	C	-		963-129
IFS 60K0.5DL	30 60	0,5 1	-	-	10	12	D	-		963-129
IFS 100K-3	75 150	1 2	-	-	25	12	D	-		963-129
IFS 100K-3L	75 150	1 2	-	-	25	20	E	-		963-129
IFS 300K-3	150 300	2 5	-	-	50	22	E	-		963-129
Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order. The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.										
IFS 6K-3SM*	3 6	1 2	1 2	20 40	1	3,8	A	965-228		963-128
IFS 6K-3M	3 6	1 2	1 2	20 40	1	5,0	B	965-228		963-128
IFS 10K-3M	6 15	2 5	2 5	40 100	2	4,8	B	965-228		963-128
IFS 10K-3LM	6 15	2 5	2 5	40 100	2	7	C	965-228		963-128
IFS 30K-3M	15 30	5 10	5 10	100 200	5	7	C	965-228		963-128
IFS 60K-2M	30 60	10 20	10 20	200 400	10	7	C	965-229		963-129
IFS 60K-2LM	30 60	10 20	10 20	200 400	10	13	D	965-229		963-129
IFS 100K-2M	60 150	20 50	20 50	400 1000	25	12	D	965-229		963-129
IFS 100K-2LM	60 150	20 50	20 50	400 1000	25	22	E	965-229		963-129

! * ONLY WHILE STOCKS LAST