

KERN KFP 60V30LM

Platform

KERN



Category

Brand	KERN
Product category	Component
Product group	Platform
Product family	KFP-V30-IP67

Measuring System

Weighing capacity [Max]	60 kg
Readability [d]	2 g
Minimum weight [Min]	400 g
Load cell connection	6-wire
Load cell OIML class	C3
Loadcell type	stainless steel IP68 encapsulated

Construction

Dimensions weighing surface (W×D)	500×400 mm
Dimensions weighing surface	500×400 mm
Dimensions weighing platform (W×D×H)	500×400×117 mm
Material weighing plate	stainless steel
Material platform	stainless steel
Material load cell(s)	aluminium
Levelling feet adjustable	✓
Cable length	3 m
Allowed cable length display device [Max]	3 m
Platform Construction	Single-Cell
Load cells - number	1

Functions

IP protection - load cell	IP67
---------------------------	------

Approval

Conformity assessment possible ex works	✓
Verification scale interval [e]	20 g

Services (optional)

Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	800×470×230 mm
Shipping method	Parcel service
Net weight approx.	14 kg
Gross weight approx.	12 kg
Shipping weight	17,3 kg

Product information

GTIN/EAN number	4045761151215
REACH classification	no prohibited substances

Pictograms

STANDARD



FACTORY

