

KERN SFE 10K-3LNM

Plattformwaage mit Staub- und Spritzwasserschutz IP65 und Eichzulassung [M]



Measuring system

Adjustment options:	External calibration
Linearity:	5 g
Readout [d]:	5 g
Recommended adjusting weight:	15 kg (M1)
Reproducibility:	5 g
Resolution:	3000
Stabilisation time:	2 s
Tare range:	14,995 kg
Warm up time:	10 min
Weighing range [Max]:	15 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height:	2,200 cm
-----------------------	----------

Technical data about verification

Minimum load [Min]:	100 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	5 g

Functions

Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

Power supply

Charging time:	12 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	AUS CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	35 h
Operating time (Backlight on):	10 h

Service

Adjustment at the location of installation:	961-248
DAkkS Certificate:	963-128
Verification:	965-228

Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	800 x 470 x 225 mm
Gross weight:	10,500 kg
Net weight:	11,540 kg
Shipping method:	Parcel service
UN number:	3496

Construction

Cable length:	2,500 m
Cable length of display device:	3 m
Dimensions of display device (WxDxH):	195 x 118 x 83 mm
Dimensions of weighing plate (WxDxH):	400 x 300 x 130 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	400 x 300 mm